



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



T20P11S2516 25KVA Ventd XFMR Eff 1PH 240X480-120/240 150C Rise *Eaton Corp*

Catalog Number	T20P11S2516
Manufacturer	Eaton Corp
Description	Eaton General Purpose Ventilated Transformer, Aluminum Windings, Nema 2, 60 HZ, 220°C, 25 Kva, Upright Only , Single-Phase, 240X480V, 120Y/240 Vac, Nema ST-20, 1 At +5%, 150°C, 25 Kva, 240 X 480 Vac-120Y/240 Vac, WS45A, 3XA, Doe 2016
Weight per unit	291.0 (lbs/each)
Product Category	20160913082725

Features

dimensions	17.0000 IN X 22.5000 IN X 33.5000 IN
Efficiency	10 CFR Part 431-2016 (DOE 2016)
Insulation Class	220 °C
kva rating	25 kVA
Number of Phases	Single-phase
Primary Voltage	240 V, 480 V
Secondary Voltage	120Y/240 V
Tap Size	1 at +5%, 2 at -5% x 2 at +2.5%, 4 at -2.5%

Descriptions

Description	25KVA VENTD XFMR EFF 1PH 240X480-120/240 150C RISE
extra long description	ETN T20P11S2516 25KVA 1PH 240X480-1
Features	Eaton types DS-3 (single-phase) and DT-3 (three-phase) general purpose ventilated dry-type transformers are two-winding, self-cooled, and available in a wide variety of primary and secondary voltage combinations. General purpose transformers are designed for continuous operation at rated kVA. They are designed, manufactured and tested in accordance with all of the latest applicable ANSI, NEMA and IEEE standards.
Long Description	Eaton General purpose ventilated transformer, Aluminum windings, NEMA 2, 60 Hz, 220°C, 25 kVA, upright only , Single-phase, 240X480V, 120Y/240 Vac, NEMA ST-20, 1 at +5%, 150°C, 25 kVA, 240 X 480 Vac-120Y/240 Vac, WS45A, 3XA, DOE 2016
Product Type	25KVA 1PH 240X480-120/240 150C
Special Features	Fungus-resistant varnished core and coil



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Eaton
GTIN	00786680147623
Manufacturers Part Number	T20P11S2516
UPC	786680147623

Taxonomies, Classifications, and Categories

Category Description	1 PHASE TRANSFORMERS
Type	Ventilated transformer

Packaging

Carton	1
Weight Per each	291

Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Power Distribution and Controls
Frequency Rating	60 Hz
Mounting standard	Floor or wall, upright only UL Listed,DOE2016 Efficient
Temperature Rating	150 °C rise