



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

8051 Bayberry Rd
32256-0000, FL Jacksonville
Phone: 904-339-8781
Fax: 904-352-2616



T81448G850DEBYP 14W Led T8 48" 50K Glass DBL Ended

Rab Lighting

Catalog Number	T81448G850DEBYP
Manufacturer	Rab Lighting
Description	Linear Tubes 1800 Lumens T8 14W 4 Feet Glass 80CRI 5000K Double Ended Wiring Method Ballast Bypass
Weight per unit	0.5600 (lbs/each)
Product Category	Shape & Circular Lamps

Features

amperage rating	102mA:120V
average life	50000
Ballast Type	Type B, Double Ended wiring
Base	G13
beam angle	210
Fixture Type	Linear Tubes
lumens	1,800
Shape	T8
total harmonic distortion	<20%
Voltage Rating	120-277
Wattage	14

Material, Color, and Finish

Color	White
color rendering index (cri)	82
color temperature	5000 (Daylight)
Finish	Matte

Dimensions and Weight

Length	4
--------	---



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

8051 Bayberry Rd
32256-0000, FL Jacksonville
Phone: 904-339-8781
Fax: 904-352-2616

Descriptions

Description	14W LED T8 48" 50K GLASS DBL ENDED
extra long description	RAB T8-14-48G-850-DE-BYP T8 LED 4ft
Long Description	Linear Tubes 1800 Lumens T8 14W 4 Feet Glass 80CRI 5000K Double Ended Wiring Method Ballast Bypass
Product Type	T8 Led 4FT 14W 5K 1800LM Dble End 25PK
Special Features	Replacement for conventional fluorescent T8 and T12 linear tubesIntegral Driver enables lamp to be wired directly to line voltage without need for an external driver or ballastDouble ended wiring methodWorks with shunted sockets.Approximately 50% more energy efficient when compared to Fluorescent T8 lamps50,000 hour Lifespan.Rated for use in enclosed and open fixtures in dry or damp locationsDiffused frosted lens will maintain the same light quality over timeInstant on full brightnessEnvironmentally friend

Manufacturer Information

Brand	RAB Lighting Inc
GTIN	00019813750811
Manufacturers Part Number	T8-14-48G-850-DE-BYP
UPC	019813750811

Taxonomies, Classifications, and Categories

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS
Type	Tubes

Packaging

Carton	1
Package	25
Weight Per each	0.56

Uses, Certifications, and Standards

Application	Indoor Lamps
-------------	--------------