



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



TB3R203 23X12X4.5 N3R 200A, 600W 4BRS TRML BX

Hoffman Enclosures, Inc.

Catalog Number	TB3R203
Manufacturer	Hoffman Enclosures, Inc.
Description	Terminal Box, Steel, Gray, Galvanized;Polyester Powder Pain, 4.50 In Overall Width, 12 In Overall Length, 23 In Overall Height, 1 Knockout, 20 LB/Ea
Weight per unit	20.0 (lbs/each)
Product Category	Nema Types 3 & 3R Metallic Enc

Features

amps	200
Phase	3Ø

Material, Color, and Finish

Color	Gray
Color Code	ANSI 61
Finish	Galvanized

Dimensions and Weight

Depth	4.5
Height	23
Size	23.00x12.00x4.50 in
Width	14

Descriptions

Description	23X12X4.5 N3R 200A,600W 4BRS TRML BX
extra long description	NVENT HOF TB3R203 3R Terminal Box 2
Features	Terminal Box, Type 3R are wire-splice boxes for outdoor commercial or industrial applications that have a feeder tap to branch circuits. Boxes are available in three- or four-wire configurations in sizes up to 400 A.

Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510144463
UPC	783510144463

Taxonomies, Classifications, and Categories

Category Description	STEEL BOXES & COVERS
Type	Utility / Canadian Cabinets and Splitters

Packaging

Carton	1
Weight Per each	20

Uses, Certifications, and Standards

nema rating	3R Weather-resistant, except dust
-------------	-----------------------------------