

Product Specifications



3/8" x 4" Phillips/Slotted Mushroom Head Toggle Bolt

Part Number TBC384

UPC 781002857907

Toggle Bolts, or butterfly anchors, are a light to medium duty anchor intended to be used in hollow block, wallboard, plaster, plywood, and other hollow base materials. Once fully opened, Toggle Bolts significantly expand the surface area making contact with the back of the hollow wall. This spreads out the load of the fastened object, increasing the weight that can be secured. The maximum weight a Toggle Bolt supports, depends on the size of the bolt and the thickness of the substrate. To accommodate the Toggle, installation requires a relatively large hole compared to other types of hollow wall anchors.



Physical Characteristics

Bit	IB3PC
Anchor Type	Toggle Bolt
Nut Type	Spring Wing
Drive Type	Phillips/Slotted
Head Type	Mushroom
Thread Style	UNC
Size	3/8" x 4"
Bit Size	#3
Anchor Diameter	3/8"
Length (in)	4"
Thread Pitch\Thread Per Inch	3/8"-16
Material	Carbon Steel
Finish	Zinc Plated

Performance Data

Pre-Drill Size	7/8"
Applications	Hollow Block, Wallboard, Plaster, Plywood and other Hollow Base Materials
Special Features	Adjustable for Various Thicknesses, Contractor Oriented Design, Easy to Use, Wings Open to Distribute Load Evenly

Packaging Details

Standard Qty	50
Master Qty	200
Price Per	100
Package Length	8.74
Package Width	5.51
Package Height	5.11
Package Weight	8.10

Certifications

RoHS Compliant	Yes
----------------	-----