



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



TC232MVOLT14GEB 8FT 4LAMP T8 Strip

Lithonia Lighting - Acuity

Catalog Number	TC232MVOLT14GEB
Manufacturer	Lithonia Lighting - Acuity
Description	Lith TC 2 32 Mvolt 1/4 GEB10IS Tand
Weight per unit	11.1 (lbs/each)
Product Category	Fluorescent Industrial Lightin

Features

average life	40,000
Ballast Type	Electronic Ballast
Hardware	No
Lamp Included	NO
Lamp Type	Fluorescent
Material	Steel
Number of Lamps	2
pallet quantity	99
Shape	Rectangular
Socket Type	Medium: Bi-pin
Voltage Rating	120 to 277
Warranty	1
Wattage	64

Material, Color, and Finish

Color	White
Finish	Gloss

Dimensions and Weight

Height	2.5
Length	96
Width	5

Descriptions

Description	8FT 4LAMP T8 STRIP
Long Description	LITH TC 2 32 MVOLT 1/4 GEB10IS Tand
Product Type	Strip Light
Special Features	For applications that require good illumination levels. Suitable for general purpose applications.



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Lithonia Lighting
GTIN	00784231159248
Manufacturers Part Number	TC 2 32 MVOLT 1/4 GEB10IS
UPC	784231159248

Taxonomies, Classifications, and Categories

Category Description	Fluorescent Fixtures & Accessories
Type	Strip Light

Trade Size

aperture size	4FT
---------------	-----

Availability

Manufacturer Status	Inactive
---------------------	----------

Packaging

Carton	1
Weight	10
Weight Per each	11.1

Uses, Certifications, and Standards

Application	Automotive & Parking, Education, Government, Healthcare, Hospitality, House of Worship, Manufacturing, Offices & Banks, Power & Gas, Residential, Retail, Sports and Recreation, Transportation, Warehouses
environmental conditions	Indoor
Mounting	Surface, Suspended
standard	UL