



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



TC926R 6" Remodel Sloped Can Non Ic Rated *Lithonia Lighting*

Catalog Number	TC926R
Manufacturer	Lithonia Lighting
Description	The Non-Ic Remodel Housing For Use In 2/12- to 6/12-Pitch Slopes, 9- to 27-Degrees, Is Ideal For Applications Where The Backside Of The Ceiling Is Not Accessible.
Weight per unit	2.9 (lbs/each)
Product Category	Incandescent Recessed Architec

Features

Lamp Type	Incandescent
Maximum Operating Temperature	25
Number of Lamps	1
Shape	OVAL

Dimensions and Weight

Height	8
Length	14
Width	8

Descriptions

Construction	Remodel
Description	6" REMODEL SLOPED CAN NON IC RATED
extra long description	LITH TC926R 6IN Incandescent Slope
Long Description	The non-IC remodel housing for use in 2/12- to 6/12-pitch slopes, 9- to 27-degrees, is ideal for applications where the backside of the ceiling is not accessible.
Product Type	Housing

Manufacturer Information

Brand	JUNO
GTIN	00661209060334
Manufacturers Part Number	TC926R
UPC	661209060334

Taxonomies, Classifications, and Categories

Category Description	All Recessed Cans & Trims
----------------------	---------------------------

Trade Size

aperture size	6 in
---------------	------

Packaging

Carton	1
Weight	11
Weight Per each	2.9



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Education, Government, Healthcare, Hospitality, House of Worship, Offices & Banks, Residential, Retail
environmental conditions	Indoor
Mounting	Recessed
standard	CSA, UL