

Eaton TCF30RN

Catalog Number: TCF30RN

Eaton Bussmann series TCF fuse, 30 A, 60 Hz, 50 Hz, Dual, CF, Black, Blade end, Time delay|Class CF, 10 sec at 500%, 300 kAIC at 600 V|100 kAIC at 300 Vdc, Glass filled PES, 35 mm DIN rail|Chassis, 600 V, 300 Vdc

General specifications



Product Name	Catalog Number
Eaton Bussmann series TCF fuse	TCF30RN
UPC	Product Length/Depth
051712220965	1.88 in
Product Height	Product Width
1.75 in	0.75 in
Product Weight	Warranty
0.08 lb	Not Applicable
Compliances	Certifications
CE Marked	UL Listed
RoHS Compliant	CSA Certified

Electrical rating

Amperage Rating

30 A

Frequency rating - max

60 Hz

Frequency rating - min

50 Hz

Interrupt rating

300 kAIC at 600 Vac

100 kAIC at 300 Vdc

Response time

10 sec at 500%

Voltage rating

600 Vac, 300 Vdc

Physical details

Color

Black

Fuse type

Class CF

Time delay

Material

Glass filled PES

Number of elements

Dual

Packaging type

Standard

General information

Class

Class CF

Connection

Blade end

Fuse indicator

Non-indicating

Mounting method

Chassis

35 mm DIN rail

Special features

Finger safe

Used with

TCFH30N, CCP2-3-30CF

Resources

Multimedia

[Bussmann series Fuseology](#)

[The Power of Space](#)

Specifications and datasheets

[Eaton Specification Sheet - TCF30RN](#)

Technical data sheets

TCF30RN-CUBEFUSE, TCF 30A NON-IND



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)