

Tamper-Resistant Floor Box Brass Cover

TM1542TRFM



Low-Profile Brass Cover requires minimum 3/8" hardwood floor thickness. Includes 885 15 amp, 125 volt Decorator Duplex receptacle and will accept any decorator device. Cover includes captive screws to prevent loss.



features & benefits

- Tamper-Resistant shutters let plugs in, keep other things out.
- Hinged door is removable and easily replaceable.
- Durable construction, impact, and scratch resistant PVC construction.
- Standard Decorator opening that accepts GFCI, TVSS, DataCom, or other Decorator devices.
- Auto/Clamps and knockouts on both sides of box.
- Meets UL514(c) scrub water exclusion test.
- Threaded device mounting holes.
- Simple mounting box, fits into a 4 3/4 inch hole and mounts with 3 screws included.
- Ready for low-voltage wiring, drill guides on underside of cover.
- UL and cUL Listed.
- Captive screws on TM1542 Series -- screws will not be lost -- new.
- Made in USA.

specifications

General Info

Product Series: Slater
Component Type: Covers & Flanges

Listing Agencies/Third Party Information

CSA Listing Info: No

CUL Listing No: No
cULus: Yes
cURus: No
Federal Spec: No
UL Listing No: No
UN SPS C: 39121308
UR: No

Dimensions

Diameter U S: 6.5"

Technical Information

Material: Brass
Floor Type: Wood

Buy American Act Compliance

Country of Origin: UNITED-STATES-OF-AMERICA
Buy American Act Status: Buy American Act Compliant