



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street  
75964-7263, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## TM8HWLICC Decor Lite & RCPT Combo

*Pass & Seymour/Legrand*

Catalog Number	TM8HWLICC
Manufacturer	Pass & Seymour/Legrand
Description	Combination Hallway Light and Receptacle, Decorator Type; Ivory Color; UI 498, UI (Canada and Us) Approval; Back, Side Wiring; Yes Wall Plate Included; Nema 5-15R 120/125 Vac 15 Ampere With Grounding Straight Blade Receptacle Type; Trademaster[R] Brand
Weight per unit	0.2600 (lbs/each)
Product Category	Combination Devices

### Features

Receptacle Type	NEMA 5-15R 2 POLE 3 WIRE WITH GROUNDING STRAIGHT BLADE
Switch Type	120/125 VAC 15 AMPERE SINGLE RECEPTACLE
Wall Plate Included	YES
Wiring	BACK, SIDE

### Material, Color, and Finish

Color	IVORY
-------	-------

### Descriptions

Additional Information	SENSOR AUTOMATICALLY TURNS LIGHT ON IN THE DARK.; HIGH IMPACT-RESISTANT LENS, FACE AND BODY
Commodity Description	COMBINATION DEVICES
Description	DECOR LITE & RCPT COMBO
Long Description	COMBINATION HALLWAY LIGHT AND RECEPTACLE, DECORATOR TYPE; IVORY COLOR; UL 498, UL (CANADA AND US) APPROVAL; BACK, SIDE WIRING; YES WALL PLATE INCLUDED; NEMA 5-15R 120/125 VAC 15 AMPERE WITH GROUNDING STRAIGHT BLADE RECEPTACLE TYPE; TRADEMASTER[R] BRAND
Product Type	Combination Hallway Light and Receptacle

### Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007009897
Manufacturers Part Number	TM8-HWLICC
UPC	785007009897

### Taxonomies, Classifications, and Categories

Category Description	Residential Switches
Type	DECORATOR

### Availability

Manufacturer Status	Non-Stock
Status	Inactive



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street  
75964-7263, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Package	12
Weight Per each	0.26

## Uses, Certifications, and Standards

Approval	UL 498, UL (CANADA AND US)
----------	----------------------------


# Straight Blade Receptacles TradeMaster® Decorator Hallway Lights & Combination Devices




Pass & Seymour




Features	
<ul style="list-style-type: none"> <li>Impact-resistant face and body.</li> <li>GE Lexan™ high impact-resistant lens.</li> <li>External screw-pressure-plate back and side wired. Accepts #12 and #14 AWG.</li> <li>Ground screw position under the end of the strap minimizes the risk of contact.</li> <li>Energy-efficient LED has average 20-year life expectancy: eliminates bulb replacement.</li> <li>Sensor automatically turns light ON in the dark.</li> </ul>	<ul style="list-style-type: none"> <li>Increased light output for better illumination.</li> <li>Light sensor for enhanced sensitivity.</li> </ul> <p><b>Tamper-Resistant Combination Version:</b></p> <ul style="list-style-type: none"> <li>UL tested shutter mechanism for protection against improper object insertion per UL478.</li> <li>Specially designed for increased protection of children in their homes.</li> <li>Superior protection than traditional outlet “caps” or “protection plates.”</li> </ul>




TMHWLCC



TMHWLECC



TM8HWLWCC



TM8HWLTRLACC

Catalog Number	Rating A. VAC	Light Output In 1' FCD*	Color	3rd Party Compliance	
				UL	UL1598
<b>TradeMaster® Decorator Full Hallway Light with Light Sensor</b>					
TMHWLCC	— 120	0.1328	Clear		•
<b>Enhanced Decorator Full Hallway Light with Light Sensor</b>					
TMHWLECC	— 120	1.079	Clear		•
<b>Enhanced Decorator Full Hallway Light without Light Sensor</b>					
TMHWLENSCC	— 120	1.113	Clear		•
<b>Full Hallway Decorator Light for use with P&amp;S Metal Louver Plates**</b>					
TMHWLLOUVCC	— 120	0.0843	Clear		•

\*FCD = Foot Candle Distance, 1 Lumen = 1 FCD. See page S-56 for more information.

\*\*For Louver Plates, see Page Q-21.

Catalog Number	Rating A. VAC	Light Output In 1' FCD*	Color	NEMA Config. No.	3rd Party Compliance	
					UL	UL498
<b>TradeMaster® Decorator Hallway Light &amp; Single Receptacle</b>						
TM8HWLICC	15 120/125	0.1442	Ivory	5-15R		•
TM8HWLWCC	15 120/125	0.1442	White	5-15R		•
TM8HWLCC	15 120/125	0.1442	Brown	5-15R		•
TM8HWLBKCC	15 120/125	0.1442	Black	5-15R		•
TM8HWLLACC	15 120/125	0.1442	Light Almond	5-15R		•
<b>Decorator Hallway Light with High Output Light &amp; Tamper-Resistant Single Receptacle</b>						
TM8HWLTRICC	15 125	0.2561	Ivory	5-15R		•
TM8HWLTRWCC	15 125	0.2561	White	5-15R		•
TM8HWLTRCC	15 125	0.2561	Brown	5-15R		•
TM8HWLTRBKCC	15 125	0.2561	Black	5-15R		•
TM8HWLTRLACC	15 125	0.2561	Light Almond	5-15R		•

\*FCD = Foot Candle Distance. 1 Lumen = 1 FCD. See page S-56 for more information.

For complete line of Decorator Combination Devices, see Pages D-9 – D-12, D-20, D-24, D-33 and D-39.

All devices listed on this page conform to NEMA WD-1 and WD-6.

Straight Blade Receptacles


Hallway Lights & Combination Devices

# Devices & Wall Plates Color Selection Chart




Pass & Seymour

## Devices & Plastic Wall Plate Colors




Ivory      Light Almond      White      Green



Black      Blue      Brown      Gray      Orange      Red


See specific device and wall plate catalog charts for particular color availabilities.

## Metal Wall Plates



**Metal Finish**      Aluminum      Brass (Brushed)      Polished Brass      Stainless Steel      Brushed Bronze      Chrome

## Custom Metal Wall Plates Paint Finish Colors



**Paint Color**      Orange      Green      Gray      Yellow      Glossy Black      Brown      White



**Paint Color**      Primer      Red      Pink      Flat Black      Ivory      Light Almond      Blue

To order custom metal wall plates, see Pages Q-43 – Q-45.

For additional colors consult factory.