

Eaton TMC7247

Catalog Number: TMC7247

Eaton Crouse-Hinds series TMC cable gland, Metal-clad, TECK corrugated or interlocked steel, or aluminum, Armoured, Aluminum, Outer sheath: 1.99-2.72", General purpose, 2-1/2" NPT, Armor range: 1.93-2.47"



General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series TMC cable gland	TMC7247
	UPC
	782274414614
Product Length/Depth	Product Height
6.19 in	4 in
Product Width	Product Weight
4 in	3 lb

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

NEMA Rating

4

Product specifications

Protection type

General purpose

Cable type

Metal-clad, TECK corrugated or interlocked steel, or aluminum

Gland type

Armoured

Material

Aluminum

Thread Size

2-1/2"

Thread type

NPT

Armor (min/max)

1.93-2.47"

Outer sheath (min/max)

1.99-2.72"

Resources

Catalogs

[Crouse-Hinds series TMC catalog page](#)

Certification reports

[TMC Armoured Gland UL certification](#)

Installation instructions

[IF 1183 - Terminator Cable Fittings](#)

Specifications and datasheets

[Eaton Specification Sheet - TMC7247](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)