

# Eaton TMCX4140 BR NP

Catalog Number: TMCX4140 BR NP

Eaton Crouse-Hinds series TMCX cable gland,Metal-cladcorrugated,TECK armoured and tray cable,Armoured barrier and non-armoured barrier, Nickel-plated brass, Outer Sheath:1.15-1.62", 1-1/4" NPT,Armor Range:1.10-1.40"



Photo is representative

## General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series TMCX cable gland	TMCX4140 BR NP
	UPC
	782274172057
Product Length/Depth	Product Height
4.1 in	2.44 in
Product Width	Product Weight
2.44 in	2.55 lb

## Certifications and compliances

### Area classification

Hazardous/Classified Locations

### Standards type

NEC/CEC

### NEC hazardous rating

Class I, Division 1

Class II, Division 1

Class III

### NEMA Rating

4

## Product specifications

### Protection type

Explosion-proof

### Cable type

Tray cable

Metal-clad with interlocked or continuously welded corrugated armoured

TECK armoured

### Gland type

Armoured Barrier and Non-armoured Barrier

### Material

Nickel plated brass

### Thread Size

1-1/4"

### Thread type

NPT

### Armor (min/max)

1.10-1.40"

### Outer sheath (min/max)

1.15-1.62"

## Resources

### Catalogs

[Crouse-Hinds series TMCX catalog page](#)

### Certification reports

[TMCX Explosionproof Armoured Barrier Gland UL certification](#)

### Installation instructions

[IF 1184 - TMCX Terminator Cable Fittings](#)

### Specifications and datasheets

[Eaton Specification Sheet - TMCX4140 BR NP](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are  
property of their respective  
owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)