

Eaton TMCX8302

Catalog Number: TMCX8302

Eaton Crouse-Hinds series TMCX cable gland, Metal-clad corrugated, TECK armoured and tray cable, Armoured barrier and non-armoured barrier, Aluminum, Outer Sheath: 2.52-3.28", 3" NPT, Armor Range: 2.45-3.02"



General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series TMCX cable gland	TMCX8302
	UPC
	782274414744
Product Length/Depth	Product Height
7.5 in	4.88 in
Product Width	Product Weight
4.88 in	7.55 lb

Certifications and compliances

Area classification

Hazardous/Classified Locations

Standards type

NEC/CEC

NEC hazardous rating

Class I, Division 1

Class II, Division 1

Class III

NEMA Rating

4

Product specifications

Protection type

Explosion-proof

Cable type

Metal-clad with interlocked or continuously welded corrugated armoured

TECK armoured

Tray cable

Gland type

Armoured Barrier and Non-armoured Barrier

Material

Aluminum

Thread Size

3"

Thread type

NPT

Armor (min/max)

2.45-3.02"

Outer sheath (min/max)

2.52-3.28"

Resources

Catalogs

[Crouse-Hinds series TMCX catalog page](#)

Certification reports

[TMCX Explosionproof Armoured Barrier Gland UL certification](#)

Installation instructions

[IF 1184 - TMCX Terminator Cable Fittings](#)

Specifications and datasheets

[Eaton Specification Sheet - TMCX8302](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)