

# Specifications



## Eaton TP163

Eaton Crouse-Hinds series Switch Box, (1) 1/2", Hold-Tite, 2, NM clamps, 2-1/2", Steel, Ears, Gangable, 12.5 cubic inch capacity

### General specifications

<b>PRODUCT NAME</b>	Eaton Crouse-Hinds series switch box
<b>CATALOG NUMBER</b>	TP163
<b>UPC</b>	786189101638
<b>PRODUCT LENGTH/DEPTH</b>	2 in
<b>PRODUCT HEIGHT</b>	3 in
<b>PRODUCT WIDTH</b>	2.5 in
<b>PRODUCT WEIGHT</b>	0.65 lb



Powering Business Worldwide

## Certifications and compliances

<b>AREA CLASSIFICATION</b>	Ordinary/Non-Hazardous Locations
<b>STANDARDS TYPE</b>	NEC/CEC

## Product specifications

<b>DEPTH</b>	2-1/2"
<b>TYPE</b>	Gangable
<b>CAPACITY</b>	12.5 cubic in
<b>CONDUIT/CABLE</b>	NM clamps
<b>BRACKET STYLE</b>	Hold-Tite
<b>BOTTOM KNOCKOUTS</b>	(1) 1/2 in
<b>CABLE KNOCKOUTS</b>	2
<b>MATERIAL</b>	Steel
<b>SPECIAL FEATURES</b>	Ears

## Resources

CATALOGS [Crouse-Hinds series Steel Switch Boxes catalog page](#)

CERTIFICATION REPORTS [Steel Switch Boxes Canadian certification](#)  
[Steel Switch Boxes UL certification](#)

SPECIFICATIONS AND DATASHEETS [Steel Outlet Boxes for Electrical Systems](#)  
[Eaton Specification Sheet - TP163](#)

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

Follow us on social media to get the latest product and support information.



© 2025 Eaton. All Rights Reserved.

# Specifications



## Eaton TP163

Eaton Crouse-Hinds series Switch Box, (1) 1/2", Hold-Tite, 2, NM clamps, 2-1/2", Steel, Ears, Gangable, 12.5 cubic inch capacity

### General specifications

<b>PRODUCT NAME</b>	Eaton Crouse-Hinds series switch box
<b>CATALOG NUMBER</b>	TP163
<b>UPC</b>	786189101638
<b>PRODUCT LENGTH/DEPTH</b>	2 in
<b>PRODUCT HEIGHT</b>	3 in
<b>PRODUCT WIDTH</b>	2.5 in
<b>PRODUCT WEIGHT</b>	0.65 lb



Powering Business Worldwide

## Certifications and compliances

<b>AREA CLASSIFICATION</b>	Ordinary/Non-Hazardous Locations
<b>STANDARDS TYPE</b>	NEC/CEC

## Product specifications

<b>DEPTH</b>	2-1/2"
<b>TYPE</b>	Gangable
<b>CAPACITY</b>	12.5 cubic in
<b>CONDUIT/CABLE</b>	NM clamps
<b>BRACKET STYLE</b>	Hold-Tite
<b>BOTTOM KNOCKOUTS</b>	(1) 1/2 in
<b>CABLE KNOCKOUTS</b>	2
<b>MATERIAL</b>	Steel
<b>SPECIAL FEATURES</b>	Ears

## Resources

CATALOGS [Crouse-Hinds series Steel Switch Boxes catalog page](#)

CERTIFICATION REPORTS [Steel Switch Boxes Canadian certification](#)  
[Steel Switch Boxes UL certification](#)

SPECIFICATIONS AND DATASHEETS [Steel Outlet Boxes for Electrical Systems](#)  
[Eaton Specification Sheet - TP163](#)

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

Follow us on social media to get the latest product and support information.



© 2025 Eaton. All Rights Reserved.