Pass and Seymour

# TradeMaster® 2-Gang Nylon Wall Plate, 1 Toggle Switch Opening, 1 Duplex Receptacle Opening, Brown

Part No. TP18

Trademaster Plate 2-Gang, 1-toggle, 1-duplex receptacle

## Features & Benefits

Molded of rugged, practically indestructible self-extinguishing nylon. ('TP' series only.)

High Impact resistant nylon face.

Available in Ivory, White, Brown, Gray, Black, Blue, Orange, Red, and Light Almond.

Preferred for hospital, industrial, institutional, and other high-abuse applications.

Nominal thickness, .070 inch.

## Specifications

### General Info

| | | | |
|---|---|---|---|
| Product Line | Pass & Seymour | Color | Brown |
| Finish | Matte | UPC Number | 785007274837 |
| Country Of Origin | Mexico | Material | Nylon |
| Construction | Plastic | Wall Plate Size | Standard Size |
| Wall Plate Type | Combination, Duplex Receptacle, Toggle Switch | Application Sector | Commercial, Residential |
| Standard | CSA, UL514 | Warranty Type | 1-Year Limited Warranty |
| Type | Wall Plate | | |

### Dimensions

| | | | |
|---|---|---|---|
| Product Width US | 4.75 in | Product Depth US | 0.25 in |
| Product Height US | 4.6875 in | | |

### Listing Agencies / 3rd Party Agencies

| | | | |
|---|---|---|---|
| cULus ListingNumber | 143222 | cULus Listed | Yes |

## Additional Information

| | |
|---|---|
| Product Environmental Profile | Yes |

## Technical Information

| | | | |
|---|---|---|---|
| Thickness | 0.07 in | Number of Gangs | 2 |
| Indoor/Outdoor | Indoor | Mounting Type | Box Mounted |
| Orientation | Vertical | | |