

# Specifications

## Eaton TP238

Eaton Crouse-Hinds series Switch Box, (1) 1/2", 2, NM clamps, 3-1/2", (1) 1/2" , Steel, (2) 1/2", Ears, Gangable, 18.0 cubic inch capacity

### General specifications

<b>PRODUCT NAME</b>	Eaton Crouse-Hinds series switch box
<b>CATALOG NUMBER</b>	TP238
<b>UPC</b>	786189102383
<b>PRODUCT LENGTH/DEPTH</b>	2 in
<b>PRODUCT HEIGHT</b>	3 in
<b>PRODUCT WIDTH</b>	3.5 in
<b>PRODUCT WEIGHT</b>	0.8 lb



Powering Business Worldwide

## Certifications and compliances

<b>AREA CLASSIFICATION</b>	Ordinary/Non-Hazardous Locations
<b>STANDARDS TYPE</b>	NEC/CEC

## Product specifications

<b>DEPTH</b>	3-1/2"
<b>TYPE</b>	Gangable
<b>CAPACITY</b>	18 cubic in
<b>CONDUIT/CABLE</b>	NM clamps
<b>END KNOCKOUTS</b>	(1) 1/2 in
<b>SIDE KNOCKOUTS</b>	(2) 1/2 in
<b>BOTTOM KNOCKOUTS</b>	(1) 1/2 in
<b>CABLE KNOCKOUTS</b>	2
<b>MATERIAL</b>	Steel
<b>SPECIAL FEATURES</b>	Ears

## Resources

<b>CATALOGS</b>	<a href="#">Crouse-Hinds series Steel Switch Boxes catalog page</a>
<b>CERTIFICATION REPORTS</b>	<a href="#">Steel Switch Boxes Canadian certification</a> <a href="#">Steel Switch Boxes UL certification</a>
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Steel Outlet Boxes for Electrical Systems</a> <a href="#">Eaton Specification Sheet - TP238</a>

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



### Eaton Corporation plc

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

Follow us on social media to get the latest product and support information.



# Specifications

## Eaton TP238

Eaton Crouse-Hinds series Switch Box, (1) 1/2", 2, NM clamps, 3-1/2", (1) 1/2" , Steel, (2) 1/2", Ears, Gangable, 18.0 cubic inch capacity

### General specifications

<b>PRODUCT NAME</b>	Eaton Crouse-Hinds series switch box
<b>CATALOG NUMBER</b>	TP238
<b>UPC</b>	786189102383
<b>PRODUCT LENGTH/DEPTH</b>	2 in
<b>PRODUCT HEIGHT</b>	3 in
<b>PRODUCT WIDTH</b>	3.5 in
<b>PRODUCT WEIGHT</b>	0.8 lb



Powering Business Worldwide

## Certifications and compliances

<b>AREA CLASSIFICATION</b>	Ordinary/Non-Hazardous Locations
<b>STANDARDS TYPE</b>	NEC/CEC

## Product specifications

<b>DEPTH</b>	3-1/2"
<b>TYPE</b>	Gangable
<b>CAPACITY</b>	18 cubic in
<b>CONDUIT/CABLE</b>	NM clamps
<b>END KNOCKOUTS</b>	(1) 1/2 in
<b>SIDE KNOCKOUTS</b>	(2) 1/2 in
<b>BOTTOM KNOCKOUTS</b>	(1) 1/2 in
<b>CABLE KNOCKOUTS</b>	2
<b>MATERIAL</b>	Steel
<b>SPECIAL FEATURES</b>	Ears

## Resources

<b>CATALOGS</b>	<a href="#">Crouse-Hinds series Steel Switch Boxes catalog page</a>
<b>CERTIFICATION REPORTS</b>	<a href="#">Steel Switch Boxes Canadian certification</a> <a href="#">Steel Switch Boxes UL certification</a>
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Steel Outlet Boxes for Electrical Systems</a> <a href="#">Eaton Specification Sheet - TP238</a>

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



### Eaton Corporation plc

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

Follow us on social media to get the latest product and support information.

