

# Specifications



## Eaton TP276

Eaton Crouse-Hinds series Octagon Outlet Box, (3) 1/2", (2) 3/4", 4", Conduit (no clamps), 1-1/2", Steel, (4) 3/4", Fixture rated, 15.5 cubic inch capacity

### General specifications

<b>PRODUCT NAME</b>	Eaton Crouse-Hinds series octagon outlet box
<b>CATALOG NUMBER</b>	TP276
<b>UPC</b>	786189102765
<b>PRODUCT LENGTH/DEPTH</b>	4 in
<b>PRODUCT HEIGHT</b>	1.5 in
<b>PRODUCT WIDTH</b>	4 in
<b>PRODUCT WEIGHT</b>	0.5 lb

## Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC

## Product specifications

BOX SIZE	4"
DEPTH	1-1/2"
CAPACITY	15.5 cubic in
CONDUIT/CABLE	Conduit (no clamps)
SIDE KNOCKOUTS	(4) 3/4 in
BOTTOM KNOCKOUTS	(3) 1/2 in, (2) 3/4 in
MATERIAL	Steel
SPECIAL FEATURES	Fixture rated

## Resources

**CATALOGS** [Crouse-Hinds series Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans catalog page](#)

**CERTIFICATION REPORTS** [Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans Canadian certification](#)  
[Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans UL certification](#)

**SPECIFICATIONS AND DATASHEETS** [Steel Outlet Boxes for Electrical Systems](#)  
[Eaton Specification Sheet - TP276](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



### Eaton Corporation plc

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

Follow us on social media to get the latest product and support information.



© 2025 Eaton. All Rights Reserved.

# Specifications



## Eaton TP276

Eaton Crouse-Hinds series Octagon Outlet Box, (3) 1/2", (2) 3/4", 4", Conduit (no clamps), 1-1/2", Steel, (4) 3/4", Fixture rated, 15.5 cubic inch capacity

### General specifications

<b>PRODUCT NAME</b>	Eaton Crouse-Hinds series octagon outlet box
<b>CATALOG NUMBER</b>	TP276
<b>UPC</b>	786189102765
<b>PRODUCT LENGTH/DEPTH</b>	4 in
<b>PRODUCT HEIGHT</b>	1.5 in
<b>PRODUCT WIDTH</b>	4 in
<b>PRODUCT WEIGHT</b>	0.5 lb

## Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC

## Product specifications

BOX SIZE	4"
DEPTH	1-1/2"
CAPACITY	15.5 cubic in
CONDUIT/CABLE	Conduit (no clamps)
SIDE KNOCKOUTS	(4) 3/4 in
BOTTOM KNOCKOUTS	(3) 1/2 in, (2) 3/4 in
MATERIAL	Steel
SPECIAL FEATURES	Fixture rated

## Resources

CATALOGS	<a href="#">Crouse-Hinds series Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans catalog page</a>
----------	---

CERTIFICATION REPORTS	<a href="#">Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans Canadian certification</a> <a href="#">Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans UL certification</a>
-----------------------	--

SPECIFICATIONS AND DATASHEETS	<a href="#">Steel Outlet Boxes for Electrical Systems</a> <a href="#">Eaton Specification Sheet - TP276</a>
-------------------------------	--

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



### Eaton Corporation plc

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

Follow us on social media to get the latest product and support information.



© 2025 Eaton. All Rights Reserved.