



Pass and Seymour
TradeMaster® 3-Gang Nylon Wall Plate, 2 Toggle Switch Openings, 1 Duplex Receptacle Opening, Brown
Part No. TP28



Trademaster Plate 3-Gang, 2-toggle, 1-duplex receptacle

Features & Benefits

Molded of rugged, practically indestructible self-extinguishing nylon. (‘TP’ series only.)

Available in Ivory, White, Brown, Gray, Black, Blue, Orange, Red, and Light Almond.

Nominal thickness, .070 inch.

High Impact resistant nylon face.

Preferred for hospital, industrial, institutional, and other high-abuse applications.

Specifications

General Info

Product Line	Pass & Seymour	Color	Brown
Finish	Matte	UPC Number	785007275124
Country Of Origin	Mexico	Material	Nylon
Construction	Plastic	Wall Plate Size	Standard Size
Wall Plate Type	Combination, Duplex Receptacle, Toggle Switch	Application Sector	Commercial, Residential
Standard	CSA, UL514	Warranty Type	1-Year Limited Warranty
Type	Wall Plate		

Dimensions

Product Width US	6.563 in	Product Depth US	0.25 in
Product Height US	4.6875 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	143222	cULus Listed	Yes
---------------------	--------	--------------	-----

Additional Information

Product Environmental Profile Yes

Technical Information

Thickness	0.07 in	Number of Gangs	3
Indoor/Outdoor	Indoor	Mounting Type	Box Mounted
Orientation	Vertical		