

Specifications



Eaton TP557

Eaton Crouse-Hinds series Square Outlet Box, (3) 1/2", (2) 3/4", 4-11/16", VS, Conduit (no clamps), Drawn, 2-1/8", Steel, (5) 1/2", (4) 1/2", (1) 3/4" C, 42.0 cubic inch capacity

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series square outlet box
CATALOG NUMBER	TP557
UPC	786189105575
PRODUCT LENGTH/DEPTH	4.69 in
PRODUCT HEIGHT	2.13 in
PRODUCT WIDTH	4.69 in
PRODUCT WEIGHT	1.2 lb



Powering Business Worldwide

Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC

Product specifications

BOX SIZE	4-11/16"
CAPACITY	42 cubic in
DEPTH	2-1/8"
CONDUIT/CABLE	Conduit (no clamps)
BRACKET STYLE	VS
CONSTRUCTION	Drawn
SIDE KNOCKOUTS	(5) 1/2 in, (4) 1/2 in, (1) 3/4 in C
BOTTOM KNOCKOUTS	(3) 1/2 in, (2) 3/4 in
MATERIAL	Steel

Resources

3D CAD DRAWING PACKAGE	Eaton Crouse-Hinds TP557 3D drawing
------------------------	---

CATALOGS	Crouse-Hinds series 4-11/16 Inch Steel Square Boxes and Covers catalog page
----------	---

CERTIFICATION REPORTS	4-11/16 Inch Steel Square Outlet Boxes, Covers, Extension Rings UL certification
-----------------------	--

CERTIFICATION REPORTS	4-11/16 Inch Steel Square Outlet Boxes, Covers, Extension Rings Canadian certification
-----------------------	--

SPECIFICATIONS AND DATASHEETS	Steel Outlet Boxes for Electrical Systems Eaton Specification Sheet - TP557
-------------------------------	--

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.



© 2025 Eaton. All Rights Reserved.