



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street  
75964-7263, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## TP604 2-1/8D Handy BX W/1/2 Ko

*Crouse-Hinds*

Catalog Number	TP604
Manufacturer	Crouse-Hinds
Description	Utility Box, Ivory, 14.5 Cu.In Capacity, 1 Gang, Rectangular, Knockout Cable Entry, 1/2 In (Bottom);1/2 In (Side) Knockout Size, 11 Knockout, Screw Mount, 4 In Length, 2-1/8 In Width, 2-1/8 In Height, 56 LB/100
Weight per unit	0.5600 (lbs/each)
Product Category	Outlet Boxes, Etc. - Steel

### Features

Material	Steel IN
----------	----------

### Dimensions and Weight

Size	2-1/8 In Width X 2-1/8 Inch Depth X 4 In Height
------	---

### Descriptions

Also Known As...	Utility Box Handy Box
Construction	Drawn
Description	2-1/8D HANDY BX W/1/2 KO

### Manufacturer Information

Brand	EATON CROUSE-HINDS SERIES
GTIN	00786189106046
UPC	786189106046

### Taxonomies, Classifications, and Categories

Category Description	HANDY BOXES
----------------------	-------------

### Packaging

Carton	1
Package	50
Weight Per each	0.56

### Uses, Certifications, and Standards

standard	UL mA
----------	-------

# Steel Utility Boxes & Covers


## UTILITY BOXES – CUBIC INCH CAPACITY (SEE BELOW)

4" LONG x 2 1/8" WIDE

UL LISTED



TP588, TP647



TP591



TP592, TP600,  
TP602



TP598, TP605



TP594, TP596



TP604, TP606

Cat. #	Bracket	Knockouts		Unit Qty.	Wt. Lbs. Per 100
		Sides	Bottom		
<b>1 1/4" Deep – 8.5 Cubic Inch Capacity</b>					
TP647	-	8 - 1/2"	3 - 1/2"	50	40
<b>1 1/2" Deep – 10.3 Cubic Inch Capacity</b>					
TP588	-	8 - 1/2"	3 - 1/2"	50	42
TP591	"F", Set 1/4"	5 - 1/2"	3 - 1/2"	50	51
<b>1 1/2" Deep Extension Rings – 10.3 Cubic Inch Capacity</b>					
TP592	-	8 - 1/2"	-	50	36
<b>1 7/8" Deep – 13.0 Cubic Inch Capacity</b>					
TP594	-	8 - 1/2"	3 - 1/2"	50	50
TP596	-	6 - 3/4"	3 - 1/2"	50	50
TP598	"S", Set 1/2"	5 - 1/2"	3 - 1/2"	50	60
<b>1 7/8" Deep Extension Rings – 13.0 Cubic Inch Capacity</b>					
TP600	-	8 - 1/2"	-	50	41
TP602	-	6 - 3/4"	-	50	41
<b>2 1/8" Deep – 14.5 Cubic Inch Capacity</b>					
TP604	-	8 - 1/2"	3 - 1/2"	50	56
TP606	-	6 - 3/4"	3 - 1/2"	50	56
TP605	"S", Set 1/2"	5 - 1/2"	3 - 1/2"	50	66

## UTILITY BOX COVERS

UL LISTED



TP608



TP610



TP612



TP613



TP614



TP616



TP618

Cat. #	Description	Unit Qty.	Wt. Lbs. Per 100
TP608*	Blank	100	10
TP610*	For 20 and 30 Amp, Twist Lock, 1 1/2" Dia.	100	9
TP612*	Single Receptacle, 1 1/2" Dia.	100	9
TP613*	For GFCI Device	100	7
TP614*	1/2" KO	100	10
TP616*	Duplex Receptacle	100	8
TP618*	One Toggle Switch	100	10

\*CSA certified.

Steel Boxes