

# Eaton TR1107LA-10-L

Catalog Number: TR1107LA-10-L

Eaton residential grade decorator duplex receptacle, Tamper resistant, 10-package, #14-10 AWG, 15A, Flush, 125V, Light almond, Brass, Impact-resistant thermoplastic face, PVC body, 5-15R, Two-pole, Three-wire, Screw,

## General specifications

Product Name	Catalog Number
Eaton residential grade decorator duplex receptacle	TR1107LA-10-L
	UPC
	032664749896
Product Length/Depth	Product Height
1.3 in	3.81 in
Product Width	Product Weight
0.69 in	0.125 lb
Certifications	
cULus Listed	
NOM	



## defaultTaxonomyAttributeLabel

### Device type

Receptacle

### Special features

Tamper resistant, 10-pckg

### Amperage Rating

15A

### Voltage rating

125V

### Contact material

Brass

### Application

Residential

### Device grade

Standard grade

### Wiring method

Side and push

### Number of wires

Three-wire

### Mounting method

Flush

### Number Of Poles

Two-pole

### Style type

Decorator

### Color

Light almond

### Connection type

Screw

### Allowable wire size

#14-10 AWG

### NEMA configuration

5-15R

### Torque rating

14 lbf-inch

## Resources

### Multimedia

[Residential straight blade receptacles](#)

### Specifications and datasheets

[Eaton Specification Sheet - TR1107LA-10-L](#)

Design type

Straight blade

Face/body material

PVC Body

Impact-resistant thermoplastic face

Receptacle type

Duplex



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)