Specifications



Photo is representative

Eaton TR1877LABXSP

Eaton commercial specification grade single receptacle, #14-10 AWG, 20A, Commercial, Flush, 125V, Side wire, Light almond, Brass, Impact-resistant thermoplastic face, PVC body, 5-20R, Single, Screw, PVC, ED Box

General specifications

PRODUCT NAME	Eaton commercial specification grade single receptacle
CATALOG NUMBER	TR1877LABXSP
UPC	032664750212
PRODUCT LENGTH/DEPTH	1.3 in
PRODUCT HEIGHT	4.19 in
PRODUCT WIDTH	0.87 in
PRODUCT WEIGHT	0.155 lb
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	cULus Listed NOM
PRODUCT TYPE	Commercial specification grade

Powering Business Worldwide

Product specifications

DEVICE TYPE	Receptacle
TYPE	Single receptacle
AMPERAGE RATING	20A
VOLTAGE RATING	125V
CONTACT MATERIAL	Brass
FEATURES	Auto-grounding Tamper resistant
APPLICATION	Commercial
DEVICE GRADE	Commercial
WIRING METHOD	Side wire
NUMBER OF WIRES	3
MOUNTING METHOD	Flush
NUMBER OF POLES	Two-pole
STYLE TYPE	Standard
MATERIAL	PVC
PACKAGING TYPE	ED Box
COLOR	Light almond
CONNECTION TYPE	Screw
ALLOWABLE WIRE SIZE	Side Wiring: #10-12 Copper or Copper Clad Aluminum
NEMA CONFIGURATION	5-20R
TORQUE RATING	14 lbf-inch
DESIGN TYPE	Straight blade
FACE/BODY MATERIAL	PVC body Impact-resistant thermoplastic face
RECEPTACLE TYPE	Single

Resources

MULTIMEDIA	Residential straight blade receptacles
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - TR1877LABXSP Commercial grade straight blade duplex receptacles spec sheet

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
DATE:	

Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

Specifications



Photo is representative

Eaton TR1877LABXSP

Eaton commercial specification grade single receptacle, #14-10 AWG, 20A, Commercial, Flush, 125V, Side wire, Light almond, Brass, Impact-resistant thermoplastic face, PVC body, 5-20R, Single, Screw, PVC, ED Box

General specifications

PRODUCT NAME	Eaton commercial specification grade single receptacle
CATALOG NUMBER	TR1877LABXSP
UPC	032664750212
PRODUCT LENGTH/DEPTH	1.3 in
PRODUCT HEIGHT	4.19 in
PRODUCT WIDTH	0.87 in
PRODUCT WEIGHT	0.155 lb
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	cULus Listed NOM
PRODUCT TYPE	Commercial specification grade

Powering Business Worldwide

Product specifications

DEVICE TYPE	Receptacle
TYPE	Single receptacle
AMPERAGE RATING	20A
VOLTAGE RATING	125V
CONTACT MATERIAL	Brass
FEATURES	Auto-grounding Tamper resistant
APPLICATION	Commercial
DEVICE GRADE	Commercial
WIRING METHOD	Side wire
NUMBER OF WIRES	3
MOUNTING METHOD	Flush
NUMBER OF POLES	Two-pole
STYLE TYPE	Standard
MATERIAL	PVC
PACKAGING TYPE	ED Box
COLOR	Light almond
CONNECTION TYPE	Screw
ALLOWABLE WIRE SIZE	Side Wiring: #10-12 Copper or Copper Clad Aluminum
NEMA CONFIGURATION	5-20R
TORQUE RATING	14 lbf-inch
DESIGN TYPE	Straight blade
FACE/BODY MATERIAL	PVC body Impact-resistant thermoplastic face
RECEPTACLE TYPE	Single

Resources

MULTIMEDIA	Residential straight blade receptacles
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - TR1877LABXSP Commercial grade straight blade duplex receptacles spec sheet

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
DATE:	

Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.