



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



TR20LA Duplex Recp TR 20A 125V La *Pass & Seymour/Legrand*

Catalog Number	TR20LA
Manufacturer	Pass & Seymour/Legrand
Description	Tamper-Resistant Commercial Grade Receptacle, 20A, 125V. Available In 6 Colors. For Detailed Tamper-Resistant Receptacle Information, Visit Our Tamper-Resistant Receptacles Page.
Weight per unit	0.2478 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

amperage rating	20
connection	Wire Ground
indoor/outdoor	Indoor
media	Yes
Mounting Type	Box
Number of Wires	3
Outlet Type	Tamper-Resistant
Poles	2
Voltage	125.0 V
Voltage Rating	125
Wall Plate Included	NO
Wire Size	14 - 10

Material, Color, and Finish

Finish	Matte
--------	-------

Dimensions and Weight

Size	3.3 in
------	--------

Descriptions

Description	DUPLEX RECP TR 20A 125V LA
extra long description	P&S TR20LA RECP DUP TAMPER RESIS 2
Features	Single Piece Plated Steel Mounting Strap
Long Description	Tamper-Resistant Commercial Grade Receptacle, 20A, 125V. Available in 6 colors. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.
Product Type	Recep Dup Tamper Resis 20A/125V La
Special Features	Side wire, easily accessed break off line contact



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007241617
Manufacturers Part Number	TR20-LA
UPC	785007241617

Taxonomies, Classifications, and Categories

Category Description	Commercial receptacles
Type	Outlet

Trade Size

Amperage	20.0
----------	------

Packaging

Carton	1
Package	100
Weight Per each	0.2478

Uses, Certifications, and Standards

Application	Commercial
Frequency Rating	60 Hz
Mounting	WALL
nema rating	5-20R
Operating Temperature	-40°-60°C
standard	CULUS, UL 498