

# Specifications

Photo is representative

## Eaton TR5262WS-SP-L

Eaton TVSS receptacle, LED indicat and alarm, #14 - #10 AWG, 15A, Comm specif, Wall/flush mnt, Bk and sd wire, 840J, 2 recept, -40° to 60°C, Wht, Brs, Strght blade, Hi-impct resist thermpls/nylon, 5-15R, Dplx 756832 756832

### General specifications

<b>PRODUCT NAME</b>	Eaton TVSS receptacle
<b>CATALOG NUMBER</b>	TR5262WS-SP-L
<b>UPC</b>	032664756832
<b>PRODUCT LENGTH/DEPTH</b>	1.62 in
<b>PRODUCT HEIGHT</b>	4.2 in
<b>PRODUCT WIDTH</b>	1.7 in
<b>PRODUCT WEIGHT</b>	0.28 lb
<b>COMPLIANCES</b>	RoHS Compliant
<b>CERTIFICATIONS</b>	cULus Listed NOM
<b>PRODUCT TYPE</b>	TVSS receptacle



Powering Business Worldwide

## Product specifications

<b>DEVICE TYPE</b>	Straight blade
<b>SPECIAL FEATURES</b>	LED indicators & alarm
<b>TYPE</b>	TVSS surge protection receptacle
<b>AMPERAGE RATING</b>	15A
<b>VOLTAGE RATING</b>	125 V
<b>CONTACT MATERIAL</b>	Brass
<b>JOULES</b>	560J
<b>ALLOWABLE WIRE SIZE</b>	Side or Back Wiring :#10-14 Copper or Copper Clad Aluminum
<b>NEMA CONFIGURATION</b>	5-15R
<b>APPLICATION</b>	Commercial
<b>DEVICE GRADE</b>	Commercial
<b>WIRING METHOD</b>	Back and side
<b>MATERIAL</b>	Thermoplastic
<b>NUMBER OF RECEPTACLES</b>	2
<b>OPERATING TEMPERATURE</b>	-40 to 60 °C
<b>TORQUE RATING</b>	14 lbf-inch
<b>NUMBER OF WIRES</b>	3
<b>MOUNTING METHOD</b>	Flush Wall
<b>NUMBER OF POLES</b>	Two-pole
<b>STYLE TYPE</b>	Duplex
<b>COLOR</b>	White
<b>FACE/BODY MATERIAL</b>	High-impact resistant thermoplastic Nylon
<b>RECEPTACLE TYPE</b>	Two-pole, three-wire, grounding

## Resources

<b>CROSS REFERENCES</b>	<a href="#">TR surge receptacles cross reference guide</a>
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton Specification Sheet - TR5262WS-SP-L</a> <a href="#">TR surge protection receptacles w/audible alarm and LED indicators spec sheet</a>

---

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**

---



**Eaton Corporation plc** Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



# Specifications

Photo is representative

## Eaton TR5262WS-SP-L

Eaton TVSS receptacle, LED indicat and alarm, #14 - #10 AWG, 15A, Comm specif, Wall/flush mnt, Bk and sd wire, 840J, 2 recept, -40° to 60°C, Wht, Brs, Strght blade, Hi-impct resist thermpls/nylon, 5-15R, Dplx 756832 756832

### General specifications

<b>PRODUCT NAME</b>	Eaton TVSS receptacle
<b>CATALOG NUMBER</b>	TR5262WS-SP-L
<b>UPC</b>	032664756832
<b>PRODUCT LENGTH/DEPTH</b>	1.62 in
<b>PRODUCT HEIGHT</b>	4.2 in
<b>PRODUCT WIDTH</b>	1.7 in
<b>PRODUCT WEIGHT</b>	0.28 lb
<b>COMPLIANCES</b>	RoHS Compliant
<b>CERTIFICATIONS</b>	cULus Listed NOM
<b>PRODUCT TYPE</b>	TVSS receptacle



Powering Business Worldwide

## Product specifications

<b>DEVICE TYPE</b>	Straight blade
<b>SPECIAL FEATURES</b>	LED indicators & alarm
<b>TYPE</b>	TVSS surge protection receptacle
<b>AMPERAGE RATING</b>	15A
<b>VOLTAGE RATING</b>	125 V
<b>CONTACT MATERIAL</b>	Brass
<b>JOULES</b>	560J
<b>ALLOWABLE WIRE SIZE</b>	Side or Back Wiring :#10-14 Copper or Copper Clad Aluminum
<b>NEMA CONFIGURATION</b>	5-15R
<b>APPLICATION</b>	Commercial
<b>DEVICE GRADE</b>	Commercial
<b>WIRING METHOD</b>	Back and side
<b>MATERIAL</b>	Thermoplastic
<b>NUMBER OF RECEPTACLES</b>	2
<b>OPERATING TEMPERATURE</b>	-40 to 60 °C
<b>TORQUE RATING</b>	14 lbf-inch
<b>NUMBER OF WIRES</b>	3
<b>MOUNTING METHOD</b>	Flush Wall
<b>NUMBER OF POLES</b>	Two-pole
<b>STYLE TYPE</b>	Duplex
<b>COLOR</b>	White
<b>FACE/BODY MATERIAL</b>	High-impact resistant thermoplastic Nylon
<b>RECEPTACLE TYPE</b>	Two-pole, three-wire, grounding

## Resources

<b>CROSS REFERENCES</b>	<a href="#">TR surge receptacles cross reference guide</a>
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton Specification Sheet - TR5262WS-SP-L</a> <a href="#">TR surge protection receptacles w/audible alarm and LED indicators spec sheet</a>

---

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**

---



**Eaton Corporation plc** Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

