



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## TR5351I SGL Recp TR 20A 125V Iv

*Pass & Seymour/Legrand*

Catalog Number	TR5351I
Manufacturer	Pass & Seymour/Legrand
Description	Tamper-Resistant Construction Spec Grade Single Receptacles, Back and Side Wire, 20A, 125V
Weight per unit	0.1732 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

### Features

amperage rating	20
connection	Back and side wire
Dielectric Strength	Withstands 2000V minimum
indoor/outdoor	Indoor
Material	Nylon
media	Yes
Number of Wires	3
Outlet Type	Tamper-Resistant
Poles	2
Voltage	125.0 V
Voltage Rating	125
Wall Plate Included	NO
Wattage	Electrical power is expressed in Amps and Volts.
Wire Size	14 - 10

### Dimensions and Weight

Height	3.28
Width	1.190

### Descriptions

Description	SGL RECP TR 20A 125V IV
extra long description	P&S TR5351I RECEP SGL TAMPER RESIS
Features	Heavy Duty Steel Mounting Strap
Long Description	Tamper-Resistant Construction Spec Grade Single Receptacles, Back and Side Wire, 20A, 125V
Product Type	Recep SGL Tamper Resis 20A/125V Iv
Special Features	Dual mechanical shutter system to help prevent insertion of foreign objects. Two drive screws anchor strap to back body and face where abrupt removal torque is greatest. Heavy-duty corrosion-resistant zinc-plated steel strap for added strength. Backed-out tri-drive steel terminal screws for faster installation. Internal screw-pressure-plate back and side wire capability. Two back wire holes for additional wiring flexibility. One-piece brass triple-wipe power contacts for lasting retention.



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007241976
Manufacturers Part Number	TR5351-I
UPC	785007241976

## Taxonomies, Classifications, and Categories

Category Description	Residential receptacles
Type	Outlet

## Trade Size

Amperage	20.0
----------	------

## Packaging

Carton	1
Package	100
Weight Per each	0.1732

## Uses, Certifications, and Standards

Application	Commercial
environmental conditions	Flammability: UL94 V2
Mounting	WALL
nema rating	5-20R
Operating Temperature	-40°-60°C
standard	CULUS, UL498, CSA C22.2 No. 42