



TR5360GYS Surge Recp TR 20A 125V Led GY

Eaton Wiring Devices

Catalog Number	TR5360GYS
Manufacturer	Eaton Wiring Devices
Description	Eaton TVSS Receptacle, Led Indicat, #14 - #10 Awg, 20A, Comm Specif, Wall/Flush MNT, BK and SD Wire, 840J, 2 Recept, -40° to 60°C, Gray, BRS, STRGHT Blade, Hi-Impct Resist Thermpls/Nylon, 5-15R, DPLX 756368 756368
Weight per unit	0.3200 (lbs/each)
Product Category	Wiring Devices

Features

media	Yes
-------	-----

Descriptions

Description	SURGE RECP TR 20A 125V LED GY
extra long description	EWD TR5360GYS SURGE RECP TR 20A 125
Features	Ideal for protecting sensitive electronic equipment, Eaton's Arrow Hart point-of-use receptacles provide branch circuit surge protection that panel-mounted devices alone cannot. Advanced diagnostic features include LED indicators to verify surge protection and ground wiring. Certain models are available with audible alarm signaling when surge protection has expired. These receptacles are also available in hospital and commercial grades with isolated ground versions.
Long Description	Eaton TVSS receptacle, LED indicat, #14 - #10 AWG, 20A, Comm specif, Wall/flush mnt, Bk and sd wire, 840J, 2 recept, -40° to 60°C, Gray, Brs, Strght blade, Hi-impct resist thermpls/nylon, 5-15R, Dplx 756368 756368
Product Type	Surge Recp TR 20A 125V Led Gy

Manufacturer Information

Brand	Eaton
GTIN	00032664756368
Manufacturers Part Number	TR5360GYS
UPC	032664756368

Taxonomies, Classifications, and Categories

Category Description	Commercial receptacles
----------------------	------------------------

Packaging

Carton	1
Package	10
Weight Per each	0.32