

Specifications



Powering Business Worldwide

Eaton TR5797

Eaton commercial specification grade single receptacle,#14-10 AWG,15A,Commercial,Floor,Recessed,125V,Back and side,Brass,Brass,Impact-resistant thermoplastic face and back body,Brass floor box,5-15R,Single,Screw,Thermoplastic,Core pack

General specifications

PRODUCT NAME	Eaton floor box with tr receptacles
CATALOG NUMBER	TR5797
UPC	032664726040
PRODUCT LENGTH/DEPTH	2.75 in
PRODUCT HEIGHT	4.5 in
PRODUCT WIDTH	3.5 in
PRODUCT WEIGHT	0.5 lb
CERTIFICATIONS	cULus Listed
PRODUCT TYPE	Floor box with TR receptacles

Product specifications

DEVICE TYPE	Receptacle
SPECIAL FEATURES	<ul style="list-style-type: none">• Tamper-resistant• Floor box assembly
TYPE	Floor box assembly
AMPERAGE RATING	15A
VOLTAGE RATING	125V
CONTACT MATERIAL	Brass
FEATURES	Tamper-resistant Floor box assembly
APPLICATION	Commercial
DEVICE GRADE	Specialty standard
WIRING METHOD	Back and side
NUMBER OF WIRES	3
MOUNTING METHOD	Recessed Floor
NUMBER OF POLES	Two-pole
STYLE TYPE	Floor box, Heavy duty
MATERIAL	Thermoplastic
PACKAGING TYPE	Core pack
COLOR	Brass
CONNECTION TYPE	Screw
ALLOWABLE WIRE SIZE	Side or Back Wiring :#10- 14 Copper or Copper Clad Aluminum
NEMA CONFIGURATION	5-15R
TORQUE RATING	14 lbf-inch
DESIGN TYPE	Straight blade
FACE/BODY MATERIAL	Impact-resistant thermoplastic face and back body Brass floor box
RECEPTACLE TYPE	Single

Resources

SPECIFICATIONS AND
DATASHEETS

[Eaton Specification Sheet -
TR5797](#)

[Recessed and floor box
receptacles spec sheet](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



Specifications



Powering Business Worldwide

Eaton TR5797

Eaton commercial specification grade single receptacle,#14-10 AWG,15A,Commercial,Floor,Recessed,125V,Back and side,Brass,Brass,Impact-resistant thermoplastic face and back body,Brass floor box,5-15R,Single,Screw,Thermoplastic,Core pack

General specifications

PRODUCT NAME	Eaton floor box with tr receptacles
CATALOG NUMBER	TR5797
UPC	032664726040
PRODUCT LENGTH/DEPTH	2.75 in
PRODUCT HEIGHT	4.5 in
PRODUCT WIDTH	3.5 in
PRODUCT WEIGHT	0.5 lb
CERTIFICATIONS	cULus Listed
PRODUCT TYPE	Floor box with TR receptacles

Product specifications

DEVICE TYPE	Receptacle
SPECIAL FEATURES	<ul style="list-style-type: none">• Tamper-resistant• Floor box assembly
TYPE	Floor box assembly
AMPERAGE RATING	15A
VOLTAGE RATING	125V
CONTACT MATERIAL	Brass
FEATURES	Tamper-resistant Floor box assembly
APPLICATION	Commercial
DEVICE GRADE	Specialty standard
WIRING METHOD	Back and side
NUMBER OF WIRES	3
MOUNTING METHOD	Recessed Floor
NUMBER OF POLES	Two-pole
STYLE TYPE	Floor box, Heavy duty
MATERIAL	Thermoplastic
PACKAGING TYPE	Core pack
COLOR	Brass
CONNECTION TYPE	Screw
ALLOWABLE WIRE SIZE	Side or Back Wiring :#10- 14 Copper or Copper Clad Aluminum
NEMA CONFIGURATION	5-15R
TORQUE RATING	14 lbf-inch
DESIGN TYPE	Straight blade
FACE/BODY MATERIAL	Impact-resistant thermoplastic face and back body Brass floor box
RECEPTACLE TYPE	Single

Resources

SPECIFICATIONS AND
DATASHEETS

[Eaton Specification Sheet -
TR5797](#)

[Recessed and floor box
receptacles spec sheet](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

