

Specifications

Photo is representative

Eaton TR6352LA-BOX

Eaton heavy-duty industrial specification grade decorator duplex receptacle, #14-10 AWG, 20A, Commercial, Flush, 125V, Back and side, Light almond, Brass, Impact-resistant thermoplastic face and back body, 5-20R, Duplex, Screw, PVC, ED Box

General specifications

PRODUCT NAME	Eaton heavy-duty industrial specification grade decorator duplex receptacle
CATALOG NUMBER	TR6352LA-BOX
UPC	032664668586
PRODUCT LENGTH/DEPTH	1.32 in
PRODUCT HEIGHT	4.19 in
PRODUCT WIDTH	0.84 in
PRODUCT WEIGHT	0.22 lb
CERTIFICATIONS	cULus Listed NOM
PRODUCT TYPE	Heavy-duty industrial specification grade



Powering Business Worldwide

Product specifications

DEVICE TYPE	Receptacle
TYPE	Duplex receptacle
AMPERAGE RATING	20A
VOLTAGE RATING	125V
CONTACT MATERIAL	Brass
FEATURES	Tamper resistant
APPLICATION	Commercial
DEVICE GRADE	Heavy-duty industrial specification grade
WIRING METHOD	Back and side
NUMBER OF WIRES	3
MOUNTING METHOD	Flush
NUMBER OF POLES	Two-pole
STYLE TYPE	Decorator
MATERIAL	PVC
PACKAGING TYPE	ED Box
COLOR	Light almond
CONNECTION TYPE	Screw
ALLOWABLE WIRE SIZE	Side or Back Wiring :#10-14 Copper or Copper Clad Aluminum
NEMA CONFIGURATION	5-20R
TORQUE RATING	14 lbf-inch
DESIGN TYPE	Straight blade
FACE/BODY MATERIAL	Impact-resistant thermoplastic face and back body
RECEPTACLE TYPE	Duplex

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:

Resources

BROCHURES	Spec grade receptacles brochure
MULTIMEDIA	Residential straight blade receptacles
	Eaton Specification Sheet - TR6352LA-BOX
SPECIFICATIONS AND DATASHEETS	Arrow Hart heavy-duty straight blade decorator receptacles



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



Specifications

Photo is representative

Eaton TR6352LA-BOX

Eaton heavy-duty industrial specification grade decorator duplex receptacle, #14-10 AWG, 20A, Commercial, Flush, 125V, Back and side, Light almond, Brass, Impact-resistant thermoplastic face and back body, 5-20R, Duplex, Screw, PVC, ED Box

General specifications

PRODUCT NAME	Eaton heavy-duty industrial specification grade decorator duplex receptacle
CATALOG NUMBER	TR6352LA-BOX
UPC	032664668586
PRODUCT LENGTH/DEPTH	1.32 in
PRODUCT HEIGHT	4.19 in
PRODUCT WIDTH	0.84 in
PRODUCT WEIGHT	0.22 lb
CERTIFICATIONS	cULus Listed NOM
PRODUCT TYPE	Heavy-duty industrial specification grade



Powering Business Worldwide

Product specifications

DEVICE TYPE	Receptacle
TYPE	Duplex receptacle
AMPERAGE RATING	20A
VOLTAGE RATING	125V
CONTACT MATERIAL	Brass
FEATURES	Tamper resistant
APPLICATION	Commercial
DEVICE GRADE	Heavy-duty industrial specification grade
WIRING METHOD	Back and side
NUMBER OF WIRES	3
MOUNTING METHOD	Flush
NUMBER OF POLES	Two-pole
STYLE TYPE	Decorator
MATERIAL	PVC
PACKAGING TYPE	ED Box
COLOR	Light almond
CONNECTION TYPE	Screw
ALLOWABLE WIRE SIZE	Side or Back Wiring :#10-14 Copper or Copper Clad Aluminum
NEMA CONFIGURATION	5-20R
TORQUE RATING	14 lbf-inch
DESIGN TYPE	Straight blade
FACE/BODY MATERIAL	Impact-resistant thermoplastic face and back body
RECEPTACLE TYPE	Duplex

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:

Resources

BROCHURES	Spec grade receptacles brochure
MULTIMEDIA	Residential straight blade receptacles
	Eaton Specification Sheet - TR6352LA-BOX
SPECIFICATIONS AND DATASHEETS	Arrow Hart heavy-duty straight blade decorator receptacles



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

