

Specifications



Photo is representative



Eaton TR6352LA-BOX

Eaton heavy-duty industrial specification grade decorator duplex receptacle, #14-10 AWG, 20A, Commercial, Flush, 125V, Back and side, Light almond, Brass, Impact-resistant thermoplastic face and back body, 5-20R, Duplex, Screw, PVC, ED Box

General specifications

PRODUCT NAME	Eaton heavy-duty industrial specification grade decorator duplex receptacle
CATALOG NUMBER	TR6352LA-BOX
UPC	032664668586
PRODUCT LENGTH/DEPTH	1.32 in
PRODUCT HEIGHT	4.19 in
PRODUCT WIDTH	0.84 in
PRODUCT WEIGHT	0.22 lb
CERTIFICATIONS	cULus Listed NOM
PRODUCT TYPE	Heavy-duty industrial specification grade

Product specifications

DEVICE TYPE	Receptacle
TYPE	Duplex receptacle
AMPERAGE RATING	20A
VOLTAGE RATING	125V
CONTACT MATERIAL	Brass
FEATURES	Tamper resistant
APPLICATION	Commercial
DEVICE GRADE	Heavy-duty industrial specification grade
WIRING METHOD	Back and side
NUMBER OF WIRES	3
MOUNTING METHOD	Flush
NUMBER OF POLES	Two-pole
STYLE TYPE	Decorator
MATERIAL	PVC
PACKAGING TYPE	ED Box
COLOR	Light almond
CONNECTION TYPE	Screw
ALLOWABLE WIRE SIZE	Side or Back Wiring :#10-14 Copper or Copper Clad Aluminum
NEMA CONFIGURATION	5-20R
TORQUE RATING	14 lbf-inch
DESIGN TYPE	Straight blade
FACE/BODY MATERIAL	Impact-resistant thermoplastic face and back body
RECEPTACLE TYPE	Duplex

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:

Resources

BROCHURES	Spec grade receptacles brochure
MULTIMEDIA	Residential straight blade receptacles
	Eaton Specification Sheet - TR6352LA-BOX
SPECIFICATIONS AND DATASHEETS	Arrow Hart heavy-duty straight blade decorator receptacles



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

