



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



TR63GRY TR Recp 20A 125V Gy

Pass & Seymour/Legrand

Catalog Number	TR63GRY
Manufacturer	Pass & Seymour/Legrand
Description	Tamper-Resistant Spec Grade Receptacles, Back and Side Wire, 20A, 125V
Weight per unit	0.2515 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

amperage rating	20
connection	Back and side wire
Dielectric Strength	Withstands 2000V minimum
indoor/outdoor	Indoor
Material	Nylon
media	Yes
Number of Wires	3
Outlet Type	Tamper-Resistant
Poles	2
Voltage	125.0 V
Voltage Rating	125
Wall Plate Included	NO
Wattage	Electrical power is expressed in Amps and Volts.
Wire Size	14 - 10

Dimensions and Weight

Height	3.281
Width	.900



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	TR RECP 20A 125V GY
extra long description	P&S TR63GRY TAMPR RESISTNT RECP 20A
Features	Brass Mounting Strap
Long Description	Tamper-Resistant Spec Grade Receptacles, Back and Side Wire, 20A, 125V
Product Type	Tampr Resistnt Recp 20A 125V Gry
Special Features	Thermoplastic dual mechanism shutter system to help prevent insertion of foreign objects. Exclusive patented feature, circuit label on face allows permanent circuit identification. Extra heavy-duty brass, one-piece mounting strap with integral ground. One-piece, brass, triple-wipe power contacts for lasting retention. Strap tabs wrap around and lock down on face to prevent strap from separating from face and back body. Impact-resistant nylon face and back body. Easily accessed break-off, line-contact conn

Manufacturer Information

Brand	Pass & Seymour/Legrand
GTIN	00785007268034
Manufacturers Part Number	TR63-GRY
UPC	785007268034

Taxonomies, Classifications, and Categories

Category Description	Residential Switches
Type	Outlet

Trade Size

Amperage	20.0
----------	------

Packaging

Carton	1
Package	100
Weight Per each	0.2515

Uses, Certifications, and Standards

Application	Commercial
environmental conditions	Flammability: UL94 V2
Mounting	WALL
nema rating	5-20R
Operating Temperature	-40°-60°C
standard	CULUS, FEDSPEC, UL498, CSA C22.2 No. 42, FEDSPEC