



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## TR63HI TR Hosp Recp 20A 125V Iv

Pass & Seymour/Legrand

Catalog Number	TR63HI
Manufacturer	Pass & Seymour/Legrand
Description	Tamper-Resistant Hospital Grade Receptacles, Back and Side Wire, 20A, 125V
Weight per unit	0.2515 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

### Features

amperage rating	20
connection	Back and side wire
Dielectric Strength	Withstands 2000V minimum
indoor/outdoor	Indoor
Material	Nylon
media	Yes
Number of Wires	3
Outlet Type	Tamper-Resistant
Poles	2
Voltage	125.0 V
Voltage Rating	125
Wall Plate Included	NO
Wattage	Electrical power is expressed in Amps and Volts.
Wire Size	14 - 10

### Material, Color, and Finish

Finish	Matte
--------	-------

### Dimensions and Weight

Height	3.281
Width	.900



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	TR HOSP RECP 20A 125V IV
extra long description	P&S TR63HI TAMPR RESISTNT HOSP RECP
Features	Brass Mounting Strap
Long Description	Tamper-Resistant Hospital Grade Receptacles, Back and Side Wire, 20A, 125V
Product Type	Tampr Resistnt Hosp Recp 20A 125V I
Special Features	Thermoplastic dual mechanism shutter system to help prevent insertion of foreign objects. Exclusive patented feature, circuit label on face allows permanent circuit identification. Extra heavy-duty brass, one-piece mounting strap with integral ground. One-piece, brass, triple-wipe power contacts for lasting retention. Strap tabs wrap around and lock down on face to prevent strap from separating from face and back body. Impact-resistant nylon face and back body. Easily accessed break-off, line-contact conne

## Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007145250
Manufacturers Part Number	TR63-HI
UPC	785007145250

## Taxonomies, Classifications, and Categories

Category Description	Commercial receptacles
Type	Outlet

## Trade Size

Amperage	20.0
----------	------

## Packaging

Carton	1
Package	100
Weight Per each	0.2515

## Uses, Certifications, and Standards

Application	Commercial
environmental conditions	Flammability: UL94 V2
Mounting	WALL
nema rating	5-20R
Operating Temperature	-40°-60°C
standard	FEDSPEC, CULUS, UL498, CSA C22.2 No. 42, FEDSPEC