

Eaton TR7730W

Catalog Number: TR7730W

Eaton commercial grade combination switch, tamp resist, auto-grnd, Decorator, #14 - #12 AWG, 15A, Commer, 120/277V switch, 125V recept, bk and sd wiring, Rocker, Maint closure, Screw, Brass, wht, 5-15R, -20-60°C, dplx, thermoplas, PVC



General specifications

Product Name	Catalog Number
Eaton commercial grade combination switch	TR7730W
	UPC
	032664750281
Product Length/Depth	Product Height
1.3 in	4.19 in
Product Width	Product Weight
1.08 in	0.277 lb
Compliances	Certifications
RoHS Compliant	cULus Listed

Product specifications

Special features

Tamper resistant, auto-ground

Connector type

Screw

Switch type

Single-pole

Configuration

Decorator

Single receptacle

Closure type

Maintained

Color

White

Wiring method

Back and side

Material

PVC

Thermoplastic

Mounting method

Flush

Allowable wire size

#14-12 AWG

Amperage Rating

15A

Number Of Poles

Single-pole

Contact type

Brass

Type

Decorator

NEMA configuration

5-15R

Device grade

Commercial

Style type

Resources

Brochures

[Decorator combination devices sell sheet](#)

Specifications and datasheets

[Eaton Specification Sheet - TR7730W](#)

Duplex

NEMA Rating

5-15R

Operating temperature

-20 to 60 °C

Voltage rating

120/277V switch, 125V receptacle

Application

Commercial

Torque rating

12-14 lbf-inch

Actuator

Rocker



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia