
Technical Data Self-test slim design <u>Tamper resistant</u> GFCI receptacles





TRGF15W

AVAILABLE IN THESE COLORS

*For ordering devices, inc	lude Cat. no. followea	by the color suffix,	for example: GF15_W
----------------------------	------------------------	----------------------	---------------------

в	вк	GY	LA	RD	v	w	SG	RB
Brown	Black	Gray	Light Almond	Red	lvory	White	Silver Granite	Oil Rubbed Bronze

MATERIALS

Housing	Top: Thermoplastic, polycarbonate Bottom: Thermoplastic, PVC
Strap	0.042" thick steel, zinc-plated
Line contacts	0.030" thick brass
Terminal	Brass/nickel-plated steel

SPECIFICATIONS

STECHTCATIONS			
Electrical	Dielectric voltage: Withstands 2000V per UL 498 Current interrupting: Yes, at full-rated current Temperature rise: Max. 30°C (86°F) after 100 cycles of overload @ 150% of rated current (DC) Trip time: 0.025 seconds (Class A) Frequency: 60 Hz; Voltage: 125V; Amperage: 15A/20A, 20A feed-through Short circuit testing: Meets and exceeds 10 kA Maximum interrupting capacity: 20 Amps		
Testing & code compliance	cULus Listed to UL 498 and UL 943, file no. E60120 Meets all UL 943 (GFCI), UL 498 (receptacles) and applicable CSA requirements; NOM certified; Federal Specification W-C-596H for 20A models		
Environmental	Flammability: Meets UL 94 requirements; V2 rated Temperature rating: -35°C to 66°C (-31°F to 150.8°F)		
Mechanical	Terminal accommodation: #14 - 10 AWG Voltage ratings: Permanently marked on device		

TRIP INDICATORS

EOL Indicator Light	RESET Button Light	Diagnosis
OFF	OFF	Device is functioning properly, OR branch circuit may not have power
OFF	ON	Device is in tripped state
Blinking or ON	ON	Device is in "end of life" state and must be replaced



Eaton 1000 Eaton Boulevard Cleveland, OH 44122 United States Eaton.com Electrical Sector 1123 Hwy 74 S Peachtree City, GA 30269 United States Eaton.com Eaton.com/wiringdevices

© 2023 Eaton All Rights Reserved Printed in USA Publication No. TD610153EN April 2023

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Arrow Hart Website Buyer's Guide Product page

DESCRIPTION			TAMPER RESISTANT
2-pole, 3-wire grounding 15A, 125V/AC 20A, 125V/AC	Elles without class NOM	5-15R	G∪ □ w} 5-20R

TAMPER RESISTANT GFCI RECEPTACLES, BACK & SIDE WIRE

Ra	ating				
Α	V/AC	NEMA	Catalog no.	Color suffix	Features
15	125	5-15R	TRGF15	B, BK, GY, LA, RB, SG, V, W	
15	125	5-15R	□TRGF15WP	W	Includes standard size wallplate
15	125	5-15R	□TRGF153-L	LA, V, W	Pack of three
20	125	5-20R	TRGF20	B, BK, GY, LA, RB, RD, SG, V, W	
20	125	5-20R	□TRGF203–L	W	Pack of three

Wallplate not included unless specifically stated; *FedSpec certification on 20A only

APPLICATIONS

- Arrow Hart GFCI receptacles are UL Listed and fully compliant with all of the latest UL943 Class A GFCI and UL498 requirements
- GFCI protection is required wherever receptacles are near wet or damp locations, such as public bathrooms, garages, and food service areas, and all other areas mandated by the NEC

DESIGN FEATURES

- Slimmer design for easy installation, leaving more room for wires in the box
- · Automatically self-tests periodically to ensure GFCI protection
- Child-safety black tamper resistant shutters help prevent improper insertion of foreign objects
- GFCIs incorporate lock-out functionality to protect against mis-wired line-load connections and GFCI circuitry damage
- Wider button wells for easy TEST and RESET
- Intuitive LED status indicators for trip and end of life states
- Clean, modern industrial design with reduced top housing markings and neutral text direction on buttons
- Meets and exceeds 10 kA short circuit testing and Underwriters Laboratories (UL) UL943 safety standards
- Automatic grounding system eliminates need for bonding jumper in grounded metal enclosure, provides redundant measure of ground continuity where jumper is used
- External backwire clamps provide visual confirmation of secure termination
- · Line side terminals are backed out and staked for fast installation

Scan QR code for additional

marketing collateral

COMPLEMENTARY PRODUCTS

Wallplates PJS26, PJS262

ADDITIONAL RESOURCES

