

Specifications



Photo is representative



Eaton TRUSBAC15W-BOX

Eaton Combination: USB Type A and C Charger, 15A 5-15R Receptacle, White, USB, Brass, Flush, Two-pole, Three-wire, Tamper resistant, Decorator

General specifications

PRODUCT NAME	Eaton combination USB charger with duplex receptacle
CATALOG NUMBER	TRUSBAC15W-BOX
UPC	032664755828
PRODUCT LENGTH/DEPTH	1.4 in
PRODUCT HEIGHT	4.19 in
PRODUCT WIDTH	1.3 in
PRODUCT WEIGHT	0.285 lb
CERTIFICATIONS	NOM cULus Listed
PRODUCT TYPE	Combination USB charger with duplex receptacle

Product specifications

TYPE	Type AC
AMPERAGE RATING	15A
VOLTAGE RATING	125 V
CONTACT MATERIAL	Brass
FEATURES	Tamper resistant 5A Charging
WIRING METHOD	Screw terminals
NUMBER OF WIRES	Three-wire
MOUNTING METHOD	Flush
NUMBER OF POLES	Two-pole
PACKAGING TYPE	Retail Box
COLOR	White
MATERIAL	Thermoplastic
STYLE	Decorator
ALLOWABLE WIRE SIZE	Side or Back Wiring :#10-14 Copper or Copper Clad Aluminum
NEMA CONFIGURATION	5-15R
TORQUE RATING	14 lbf-inch
COMBINATION TYPE	USB
DESIGN TYPE	Receptacle
RECEPTACLE TYPE	Two-pole, three-wire, grounding

Resources

BROCHURES	5A Slim USB Charging Receptacles
MULTIMEDIA	Introduction to USB-C Duplex Receptacles Fast and convenient charging made easy with Eaton's USB receptacles Eaton's USB charging receptacles - Never miss a moment
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - TRUSBAC15W-BOX USB A/C charger tamper resistant receptacle spec sheet

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

