


# Specifications



Photo is representative



## Eaton TRUSBAC20W-BOX

Eaton Combination USB Type A and C Charger, 20A 5-20R Receptacle, White, USB, Brass, Thermoplastic, Flush, Two-pole, Three-wire, Tamper resistant, Decorator, 125V

### General specifications

<b>PRODUCT NAME</b>	Eaton combination USB charger with duplex receptacle
<b>CATALOG NUMBER</b>	TRUSBAC20W-BOX
<b>UPC</b>	032664755941
<b>PRODUCT LENGTH/DEPTH</b>	1.4 in
<b>PRODUCT HEIGHT</b>	4.19 in
<b>PRODUCT WIDTH</b>	1.3 in
<b>PRODUCT WEIGHT</b>	0.285 lb
<b>WARRANTY</b>	1 year
<b>CERTIFICATIONS</b>	NOM cULus Listed
<b>PRODUCT TYPE</b>	Combination USB charger with duplex receptacle



Powering Business Worldwide

## Product specifications

<b>TYPE</b>	Type AC
<b>AMPERAGE RATING</b>	20A
<b>VOLTAGE RATING</b>	125 V
<b>CONTACT MATERIAL</b>	Brass
<b>FEATURES</b>	Tamper resistant 5A Charging
<b>WIRING METHOD</b>	Screw terminals
<b>NUMBER OF WIRES</b>	Three-wire
<b>MOUNTING METHOD</b>	Flush
<b>NUMBER OF POLES</b>	Two-pole
<b>PACKAGING TYPE</b>	Retail Box
<b>COLOR</b>	White
<b>MATERIAL</b>	Thermoplastic
<b>STYLE</b>	Decorator
<b>ALLOWABLE WIRE SIZE</b>	Side or Back Wiring :#10- 14 Copper or Copper Clad Aluminum
<b>NEMA CONFIGURATION</b>	5-20R
<b>TORQUE RATING</b>	14 lbf-inch
<b>COMBINATION TYPE</b>	USB
<b>DESIGN TYPE</b>	Receptacle
<b>RECEPTACLE TYPE</b>	Two-pole, three-wire, grounding

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**

## Resources

<b>BROCHURES</b>	<a href="#">5A Slim USB Charging Receptacles</a>
<b>MULTIMEDIA</b>	<a href="#">Eaton's USB charging receptacles - Never miss a moment</a> <a href="#">Fast and convenient charging made easy with Eaton's USB receptacles</a> <a href="#">Introduction to USB-C Duplex Receptacles</a> <a href="#">Eaton Specification Sheet - TRUSBAC20W-BOX</a>
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">USB A/C charger tamper resistant receptacle spec sheet</a>



**Eaton Corporation plc** Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



# Specifications



Photo is representative



## Eaton TRUSBAC20W-BOX

Eaton Combination USB Type A and C Charger, 20A 5-20R Receptacle, White, USB, Brass, Thermoplastic, Flush, Two-pole, Three-wire, Tamper resistant, Decorator, 125V

### General specifications

<b>PRODUCT NAME</b>	Eaton combination USB charger with duplex receptacle
<b>CATALOG NUMBER</b>	TRUSBAC20W-BOX
<b>UPC</b>	032664755941
<b>PRODUCT LENGTH/DEPTH</b>	1.4 in
<b>PRODUCT HEIGHT</b>	4.19 in
<b>PRODUCT WIDTH</b>	1.3 in
<b>PRODUCT WEIGHT</b>	0.285 lb
<b>WARRANTY</b>	1 year
<b>CERTIFICATIONS</b>	NOM cULus Listed
<b>PRODUCT TYPE</b>	Combination USB charger with duplex receptacle

## Product specifications

<b>TYPE</b>	Type AC
<b>AMPERAGE RATING</b>	20A
<b>VOLTAGE RATING</b>	125 V
<b>CONTACT MATERIAL</b>	Brass
<b>FEATURES</b>	Tamper resistant 5A Charging
<b>WIRING METHOD</b>	Screw terminals
<b>NUMBER OF WIRES</b>	Three-wire
<b>MOUNTING METHOD</b>	Flush
<b>NUMBER OF POLES</b>	Two-pole
<b>PACKAGING TYPE</b>	Retail Box
<b>COLOR</b>	White
<b>MATERIAL</b>	Thermoplastic
<b>STYLE</b>	Decorator
<b>ALLOWABLE WIRE SIZE</b>	Side or Back Wiring :#10- 14 Copper or Copper Clad Aluminum
<b>NEMA CONFIGURATION</b>	5-20R
<b>TORQUE RATING</b>	14 lbf-inch
<b>COMBINATION TYPE</b>	USB
<b>DESIGN TYPE</b>	Receptacle
<b>RECEPTACLE TYPE</b>	Two-pole, three-wire, grounding

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**

## Resources

<b>BROCHURES</b>	<a href="#">5A Slim USB Charging Receptacles</a>
<b>MULTIMEDIA</b>	<a href="#">Eaton's USB charging receptacles - Never miss a moment</a> <a href="#">Fast and convenient charging made easy with Eaton's USB receptacles</a> <a href="#">Introduction to USB-C Duplex Receptacles</a> <a href="#">Eaton Specification Sheet - TRUSBAC20W-BOX</a>
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">USB A/C charger tamper resistant receptacle spec sheet</a>



**Eaton Corporation plc** Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

