



Powering Business Worldwide

TRVGF15A

GFCI TR Deco Duplex 15A 125V AL

UPC: 032664665653

Brand Name: Arrow Hart

Sub Brand: Hart-Lock

Type: Flanged Outlet, Locking

Special Features: Wiring Type Back Wire

Application: Industrial

Number Of Poles: 3

Number Of Wires: 3

Wire Size: 14 To 8 AWG

Amperage Rating: 30 Amp

Voltage Rating: 250 Vac

Phase: 3

Material: Nylon Housing/Interior Body, Polycarbonate Terminal Retainer

Color: Black, White

NEMA Rating: L11-30

TRVGF15A-3

GFCI TR Deco Dup 15A 125V 3PK NoWlplt AL

UPC: 032664665660

Brand Name: Arrow Hart

Sub Brand: Hart-Lock

Type: Flanged Outlet, Locking

Special Features:

Application: Industrial

Number Of Poles: 3

Number Of Wires: 3

Amperage Rating: 30 Amp

Voltage Rating: 480 Vac

Phase: 3

Color: Black, White

NEMA Rating: L12-30

TRVGF15A-AG

GFCI TR Deco Duplex 15A 125V Auto GND AL

UPC: 032664733635

Brand Name: Arrow Hart

Sub Brand: Hart-Lock

Type: Flanged Inlet

Special Features:

Application: Industrial

Number Of Poles: 3

Number Of Wires: 3

Amperage Rating: 30 Amp

Voltage Rating: 600 Vac

Color: Black, White

NEMA Rating: L13-30

Size: 2.87 In Diameter X 1.95 In Height



Powering Business Worldwide

TRVGF15A-BXC

GFCI TR Deco Duplex 15A 125V AL CAN

UPC: 032664665677

Brand Name: Arrow Hart

Sub Brand: Hart-Lock

Type: Flanged Outlet, Locking

Special Features:

Application: Industrial

Number Of Poles: 3

Number Of Wires: 3

Amperage Rating: 30 Amp

Voltage Rating: 600 Vac

Phase: 3

Color: Black, White

NEMA Rating: L13-30

TRVGF15A-M

GFCI TR Deco Dup 15A 125V W/Mid Wlplt AL

UPC: 032664667787

Brand Name: Eaton

Sub Brand: Eaton

Type: Flanged Insert

Special Features: Wiring Type Back Wire, Grounding

Application: Industrial

Number Of Poles: 3

Number Of Wires: 4

Wire Size: 14 To 8 AWG

Amperage Rating: 20 Amp

Voltage Rating: 125/250 Vac

Cord Type: 0.38 To 1.00 In Diameter

Material: Nylon Outer Shell/Interior Body, Polycarbonate Terminal Retainer

Color: Black, White

NEMA Rating: L14-20

Connection: Screw

Size: 3.06 In Diameter X 2.19 In Height

Environmental Conditions: -40 To 60 Deg C



Powering Business Worldwide

TRVGF15B

GFCI TR Deco Duplex 15A 125V BR

UPC: 032664665684

Brand Name: Arrow Hart

Sub Brand: Hart-Lock

Type: Flanged Outlet, Locking

Special Features: Wiring Type Back Wire

Application: Industrial

Number Of Poles: 3

Number Of Wires: 4

Wire Size: 14 To 8 AWG

Amperage Rating: 20 Amp

Voltage Rating: 125/250 Vac

Material: Nylon Housing/Interior Body, Polycarbonate Terminal Retainer

Color: Black, White

NEMA Rating: L14-20

TRVGF15B-AG

GFCI TR Deco Duplex 15A 125V Auto GND BR

UPC: 032664733642

Brand Name: Eaton

Sub Brand: Eaton

Type: Flanged Inlet

Special Features: Wiring Type Back Wire

Application: Industrial

Number Of Poles: 3

Number Of Wires: 4

Wire Size: 14 To 8 AWG

Amperage Rating: 20 Amp

Voltage Rating: 250 Vac

Cord Type: 0.63 To 1.16 In Diameter

Material: Nylon Flanged Housing/Interior Body, Polycarbonate Terminal Retainer

Color: Black, White

NEMA Rating: L15-20

Connection: Screw

Environmental Conditions: '-40 To 60 Deg C



Powering Business Worldwide

TRVGF15BK-AG

GFCI TR Deco Duplex 15A 125V Auto GND BK

UPC: 032664716669

Brand Name: Arrow Hart

Sub Brand: Hart-Lock

Type: Flanged Outlet, Locking

Special Features: Wiring Type Back Wire

Application: Industrial

Number Of Poles: 3

Number Of Wires: 4

Wire Size: 14 To 8 AWG

Amperage Rating: 20 Amp

Voltage Rating: 250 Vac

Material: Nylon Housing/Interior Body, Polycarbonate Terminal Retainer

Color: Black, White

NEMA Rating: L15-20

TRVGF15BKM

GFCI TR Deco Duplex 15A 125V MOD BK

UPC: 032664676215

Brand Name: Arrow Hart

Sub Brand: Hart-Lock

Type: Flanged Inlet

Special Features: Wiring Type Back Wire

Application: Industrial

Number Of Poles: 3

Number Of Wires: 4

Wire Size: 14 To 8 AWG

Amperage Rating: 20 Amp

Voltage Rating: 480 Vac

Material: Nylon Flanged Housing/Interior Body, Polycarbonate Terminal Retainer

Color: Black, White

NEMA Rating: L16-20



Powering Business Worldwide

TRVGF15BKSPL

GFCI TR Deco Duplex 15A 125V BK

UPC: 032664665691

Brand Name: Eaton

Sub Brand: Eaton

Type: Flanged Outlet, Locking

Special Features: Wiring Type Back Wire

Application: Industrial

Number Of Poles: 3

Number Of Wires: 4

Wire Size: 14 To 8 AWG

Amperage Rating: 20 Amp

Voltage Rating: 480 Vac

Phase: 3

Cord Type: 0.38 To 1.00 In Diameter

Material: Nylon Housing/Interior Body, Polycarbonate Terminal Retainer

Color: Black, White

NEMA Rating: L16-20

Connection: Screw

Size: 3.06 In Diameter X 2.19 In Height

Environmental Conditions: -40 To 60 Deg C

TRVGF15BM

GFCI TR Deco Duplex 15A 125V MOD BR

UPC: 032664676222

Brand Name: Eaton

Sub Brand: Eaton

Type: Flanged Insert

Special Features: Wiring Type Back Wire, Grounding

Application: Industrial

Number Of Poles: 3

Number Of Wires: 4

Wire Size: 14 To 8 AWG

Amperage Rating: 30 Amp

Voltage Rating: 125/250 Vac

Cord Type: 0.63 To 1.16 In Diameter

Material: Nylon Outer Shell/Interior Body, Polycarbonate Terminal Retainer

Color: Black, White

NEMA Rating: L14-30

Connection: Screw

Size: 3.06 In Diameter X 2.19 In Height

Environmental Conditions: -40 To 60 Deg C



Powering Business Worldwide

TRVGF15FB

GFCI TR Deco Duplex 15A 125V BR NAFTA

UPC: 032664713798

Brand Name: Arrow Hart

Sub Brand: Hart-Lock

Type: Flanged Outlet, Locking

Special Features: Wiring Type Back Wire

Application: Industrial

Number Of Poles: 3

Number Of Wires: 4

Wire Size: 14 To 8 AWG

Amperage Rating: 30 Amp

Voltage Rating: 125/250 Vac

Material: Nylon Housing/Interior Body, Polycarbonate Terminal Retainer

Color: Black, White

NEMA Rating: L14-30

TRVGF15FBK

GFCI TR Deco Duplex 15A 125V BK NAFTA

UPC: 032664713804

Brand Name: Eaton

Sub Brand: Eaton

Type: Flanged Inlet

Special Features: Wiring Type Back Wire

Application: Industrial

Number Of Poles: 3

Number Of Wires: 4

Wire Size: 14 To 8 AWG

Amperage Rating: 30 Amp

Voltage Rating: 250 Vac

Cord Type: 0.63 To 1.16 In Diameter

Material: Nylon Flanged Housing/Interior Body, Polycarbonate Terminal Retainer

Color: Black, White

NEMA Rating: L15-30

Connection: Screw

Size: 3.06 In Diameter X 2.19 In Height

Environmental Conditions: '-40 To 60 Deg C



Powering Business Worldwide

TRVGF15FGY

GFCI TR Deco Duplex 15A 125V GY NAFTA

UPC: 032664713811

Brand Name: Eaton

Sub Brand: Eaton

Type: Flanged Outlet, Locking

Special Features: Wiring Type Back Wire

Application: Industrial

Number Of Poles: 3

Number Of Wires: 4

Wire Size: 14 To 8 AWG

Amperage Rating: 30 Amp

Voltage Rating: 250 Vac

Phase: 3

Cord Type: 0.63 To 1.16 In Diameter

Material: Nylon Housing/Interior Body, Polycarbonate Terminal Retainer

Color: Black, White

NEMA Rating: L15-30

Connection: Screw

Size: 3.06 In Diameter X 2.19 In Height

Environmental Conditions: '-40 To 60 Deg C

TRVGF15FLA

GFCI TR Deco Duplex 15A 125V LA NAFTA

UPC: 032664713828

Brand Name: Eaton

Sub Brand: Eaton

Type: Flanged Inlet

Special Features: Wiring Type Back Wire

Application: Industrial

Number Of Poles: 3

Number Of Wires: 4

Wire Size: 14 To 8 AWG

Amperage Rating: 30 Amp

Voltage Rating: 480 Vac

Phase: 3

Cord Type: 0.63 To 1.16 In Diameter

Material: Nylon Flanged Housing/Interior Body, Polycarbonate Terminal Retainer

Color: Black, White

NEMA Rating: L16-30

Connection: Screw

Size: 3.06 In Diameter X 2.19 In Height

Environmental Conditions: '-40 To 60 Deg C



Powering Business Worldwide

TRVGF15FRD

GFCI TR Deco Duplex 15A 125V RD NAFTA

UPC: 032664713835

Brand Name: Eaton

Sub Brand: Eaton

Type: Flanged Outlet, Locking

Special Features: Wiring Type Back Wire

Application: Industrial

Number Of Poles: 3

Number Of Wires: 4

Wire Size: 14 To 8 AWG

Amperage Rating: 30 Amp

Voltage Rating: 480 Vac

Phase: 3

Cord Type: 0.63 To 1.16 In Diameter

Material: Nylon Housing/Interior Body, Polycarbonate Terminal Retainer

Color: Black, White

NEMA Rating: L16-30

Connection: Screw

Size: 3.06 In Diameter X 2.19 In Height

Environmental Conditions: '-40 To 60 Deg C

TRVGF15FV

GFCI TR Deco Duplex 15A 125V IV NAFTA

UPC: 032664713842

Brand Name: Arrow Hart

Sub Brand: Hart-Lock

Type: Flanged Inlet

Special Features: Wiring Type Back Wire

Application: Industrial

Number Of Poles: 3

Number Of Wires: 4

Wire Size: 14 To 8 AWG

Amperage Rating: 30 Amp

Voltage Rating: 600 Vac

Phase: 3

Material: Nylon Flanged Housing/Interior Body, Polycarbonate Terminal Retainer

Color: Black, White

NEMA Rating: L17-30

Size: 3.06 In Diameter X 2.19 In Height



Powering Business Worldwide

TRVGF15FW

GFCI TR Deco Duplex 15A 125V WH NAFTA

UPC: 032664713859

Brand Name: Eaton

Sub Brand: Eaton

Type: Locking, Flanged

Special Features: Wiring Type Back Wire

Application: Industrial

Number Of Poles: 3

Number Of Wires: 4

Wire Size: 14 To 8 AWG

Amperage Rating: 30 Amp

Voltage Rating: 600 Vac

Phase: 3

Cord Type: 0.63 To 1.16 In Diameter

Material: Nylon Flanged Housing/Interior Body, Polycarbonate Terminal Retainer

Color: Black, White

NEMA Rating: L17-30

Connection: Screw

Environmental Conditions: -40 To 60 Deg C

TRVGF15GY

GFCI TR Deco Duplex 15A 125V GY

UPC: 032664665707



Powering Business Worldwide

TRVGF15GY-AG

GFCI TR Deco Duplex 15A 125V Auto GND GY

UPC: 032664733659

Brand Name: Arrow Hart

Sub Brand: Hart-Lock

Type: Flanged Outlet, Locking

Special Features: Non-NEMA, Wiring Type Back Wire

Application: Industrial

Number Of Poles: 4

Number Of Wires: 4

Wire Size: 14 To 8 AWG

Amperage Rating: 20 Amp

Voltage Rating: 120/208 Vac

Phase: 3

Material: Nylon Housing/Interior Body, Polycarbonate Terminal Retainer

Color: Gray

TRVGF15GYM

GFCI TR Deco Duplex 15A 125V MOD GY

UPC: 032664676239

Brand Name: Arrow Hart

Sub Brand: Hart-Lock

Type: Flanged Inlet

Special Features: Wiring Type Back Wire

Application: Industrial

Number Of Poles: 4

Number Of Wires: 4

Wire Size: 14 To 8 AWG

Amperage Rating: 20 Amp

Voltage Rating: 120/208 Vac

Phase: 3

Material: Nylon Flanged Housing/Interior Body, Polycarbonate Terminal Retainer

Color: Black, White

NEMA Rating: L18-20

Size: 3.06 In Diameter X 2.19 In Height



Powering Business Worldwide

TRVGF15LA

GFCI TR Deco Duplex 15A 125V LA

UPC: 032664665714

Brand Name: Arrow Hart

Sub Brand: Hart-Lock

Type: Flanged Outlet, Locking

Special Features: Wiring Type Back Wire

Application: Industrial

Number Of Poles: 4

Number Of Wires: 4

Wire Size: 14 To 8 AWG

Amperage Rating: 20 Amp

Voltage Rating: 120/208 Vac

Phase: 3

Material: Nylon Housing/Interior Body, Polycarbonate Terminal Retainer

Color: Black, White

NEMA Rating: L18-20

TRVGF15LA-3

GFCI TR Deco Dup 15A 125V 3PK NoWlplt LA

UPC: 032664665721

Brand Name: Arrow Hart

Sub Brand: Hart-Lock

Type: Flanged Inlet

Special Features: Wiring Type Back Wire

Application: Industrial

Number Of Poles: 4

Number Of Wires: 4

Wire Size: 14 To 8 AWG

Amperage Rating: 20 Amp

Voltage Rating: 277/480 Vac

Phase: 3

Material: Nylon Flanged Housing/Interior Body, Polycarbonate Terminal Retainer

Color: Black, White

NEMA Rating: L19-20

Size: 3.06 In Diameter X 2.19 In Height



Powering Business Worldwide

TRVGF15LA-AG

GFCI TR Deco Duplex 15A 125V Auto GND IV

UPC: 032664733666

Brand Name: Arrow Hart

Sub Brand: Hart-Lock

Type: Flanged Outlet, Locking

Special Features: Wiring Type Back Wire

Application: Industrial

Number Of Poles: 4

Number Of Wires: 4

Wire Size: 14 To 8 AWG

Amperage Rating: 20 Amp

Voltage Rating: 277/480 Vac

Phase: 3

Material: Nylon Housing/Interior Body, Polycarbonate Terminal Retainer

Color: Black, White

NEMA Rating: L19-20

TRVGF15LA-M

GFCI TR Deco Dup 15A 125V W/Mid Wlplt LA

UPC: 032664667794

Brand Name: Arrow Hart

Sub Brand: Hart-Lock

Type: Flanged Inlet

Special Features: Wiring Type Back Wire

Application: Industrial

Number Of Poles: 4

Number Of Wires: 4

Wire Size: 14 To 8 AWG

Amperage Rating: 20 Amp

Voltage Rating: 347/600 Vac

Phase: 3

Material: Nylon Flanged Housing/Interior Body, Polycarbonate Terminal Retainer

Color: Black, White

NEMA Rating: L20-20

Size: 3.06 In Diameter X 2.19 In Height



Powering Business Worldwide

TRVGF15V

GFCI TR Deco Duplex 15A 125V IV

UPC: 032664665745

Brand Name: Arrow Hart

Sub Brand: Hart-Lock

Type: Flanged Outlet, Locking

Special Features: Wiring Type Back Wire

Application: Industrial

Number Of Poles: 4

Number Of Wires: 4

Wire Size: 14 To 8 AWG

Amperage Rating: 20 Amp

Voltage Rating: 347/600 Vac

Phase: 3

Material: Nylon Housing/Interior Body, Polycarbonate Terminal Retainer

Color: Black, White

NEMA Rating: L20-20

TRVGF15V-3

GFCI TR Deco Dup 15A 125V 3PK NoWlplt IV

UPC: 032664665752

Brand Name: Arrow Hart

Sub Brand: Hart-Lock

Type: Flanged Inlet

Special Features: Non-NEMA, Wiring Type Back Wire

Application: Industrial

Number Of Poles: 4

Number Of Wires: 4

Wire Size: 14 To 8 AWG

Amperage Rating: 30 Amp

Voltage Rating: 120/208 Vac

Phase: 3

Material: Nylon Outer Shell/Interior Body, Polycarbonate Terminal Retainer

Color: Black, White

Size: 3.06 In Diameter X 2.19 In Height



Powering Business Worldwide

TRVGF15V-AG

GFCI TR Deco Duplex 15A 125V Auto GND WH

UPC: 032664716690

Brand Name: Arrow Hart

Sub Brand: Hart-Lock

Type: Flanged Outlet, Locking

Special Features: Non-NEMA, Wiring Type Back Wire

Application: Industrial

Number Of Poles: 4

Number Of Wires: 4

Wire Size: 14 To 8 AWG

Amperage Rating: 30 Amp

Voltage Rating: 120/208 Vac

Phase: 3

Material: Nylon Outer Shell/Interior Body, Polycarbonate Terminal Retainer

Color: Black, White

TRVGF15V-BXC

GFCI TR Deco Duplex 15A 125V IV CAN

UPC: 032664665769

Brand Name: Arrow Hart

Sub Brand: Hart-Lock

Type: Flanged Inlet

Special Features: Wiring Type Back Wire

Application: Industrial

Number Of Poles: 4

Number Of Wires: 4

Wire Size: 14 To 8 AWG

Amperage Rating: 30 Amp

Voltage Rating: 120/208 Vac

Phase: 3

Material: Nylon Flanged Housing/Interior Body, Polycarbonate Terminal Retainer

Color: Black, White

NEMA Rating: L18-30

Size: 3.06 In Diameter X 2.19 In Height



Powering Business Worldwide

TRVGF15V-M

GFCI TR Deco Dup 15A 125V W/Mid Wlplt IV

UPC: 032664667800

Brand Name: Arrow Hart

Sub Brand: Hart-Lock

Type: Flanged Outlet, Locking

Special Features: Wiring Type Back Wire

Application: Industrial

Number Of Poles: 4

Number Of Wires: 4

Wire Size: 14 To 8 AWG

Amperage Rating: 30 Amp

Voltage Rating: 120/208 Vac

Phase: 3

Material: Nylon Housing/Interior Body, Polycarbonate Terminal Retainer

Color: Black, White

NEMA Rating: L18-30

TRVGF15W

GFCI TR Deco Duplex 15A 125V WH

UPC: 032664665776

Brand Name: Arrow Hart

Sub Brand: Hart-Lock

Type: Flanged Inlet

Special Features: Wiring Type Back Wire

Application: Industrial

Number Of Poles: 4

Number Of Wires: 4

Wire Size: 14 To 8 AWG

Amperage Rating: 30 Amp

Voltage Rating: 277/480 Vac

Phase: 3

Material: Nylon Flanged Housing/Interior Body, Polycarbonate Terminal Retainer

Color: Black, White

NEMA Rating: L19-30



Powering Business Worldwide

TRVGF15W-3-C

GFCI TR Deco Duplex 15A 125V WH CAN

UPC: 032664665783

Brand Name: Arrow Hart

Sub Brand: Hart-Lock

Type: Locking, Flanged

Special Features: Wiring Type Back Wire

Application: Industrial

Number Of Poles: 4

Number Of Wires: 4

Wire Size: 14 To 8 AWG

Amperage Rating: 30 Amp

Voltage Rating: 277/480 Vac

Phase: 3

Material: Nylon Flanged Housing/Interior Body, Polycarbonate Terminal Retainer

Color: Black, White

NEMA Rating: L19-30

Connection: Screw

TRVGF15W-BXC

GFCI TR Deco Duplex 15A 125V WH CAN

UPC: 032664665790

Brand Name: Arrow Hart

Sub Brand: Hart-Lock

Type: Flanged Inlet

Special Features: Wiring Type Back Wire

Application: Industrial

Number Of Poles: 4

Number Of Wires: 4

Wire Size: 14 To 8 AWG

Amperage Rating: 30 Amp

Voltage Rating: 347/600 Vac

Phase: 3

Material: Nylon Flanged Housing/Interior Body, Polycarbonate Terminal Retainer

Color: Black, White

NEMA Rating: L20-30

Size: 3.06 In Diameter X 2.19 In Height



Powering Business Worldwide

TRVGF15W-M

GFCI TR Deco Dup 15A 125V W/Mid Wlplt WH

UPC: 032664667817

Brand Name: Arrow Hart

Sub Brand: Hart-Lock

Type: Flanged Outlet, Locking

Special Features: Wiring Type Back Wire

Application: Industrial

Number Of Poles: 4

Number Of Wires: 4

Wire Size: 14 To 8 AWG

Amperage Rating: 30 Amp

Voltage Rating: 347/600 Vac

Phase: 3

Material: Nylon Housing/Interior Body, Polycarbonate
Terminal Retainer

Color: Black, White

NEMA Rating: L20-30