



Pass and Seymour
Discontinued - TradeMaster® LED/CFL/Incandescent Single Pole/3-Way Toggle Slide Dimmer, Preset, Tri-Color
Part No. TSDCL303PTC



TradeMaster® Toggle Slide Dimmer is designed for use with compact fluorescent or LED lighting fixtures. This single pole 3-way switch can be used in a two-location layout. The slide can be set to your preferred level and then toggle on and off providing instant repeatability. This switch offers dependability and a lifetime warranty.

Features & Benefits

Matches appearance of standard Pass and Seymour toggle switch
Interchangeable face covers are available in seven different colors
Lifetime warranty

All models are Single Pole/3-Way capable
Highest wattage rating

Specifications

General Info

Product Line	Pass & Seymour	Replaced by Part Number	TSDL153PTC
Color	Ivory, Light Almond, White	Finish	Gloss
UPC Number	785007215977	Country Of Origin	China
Material	Steel, Thermoplastic	Product Series	Trademaster
Features	Color Change Kit, Low-End Trim (Dim Range)	Switch Type	Slider, Toggle
Number of Switches	1	Application Sector	Residential
Warranty Type	Limited Lifetime Warranty		

Dimensions

Product Width US	2.5 in	Product Depth US	1.4 in
Product Height US	4.19 in		

Technical Information

Preset	Yes	Load Rating	120V 2.5A 300W (LED), 120V 4.5A 450W (CFL), 120V 700W (Halogen), 120V 700W (Incandescent)
Dimming Compatibility	Forward Phase	Frequency Rating	60 Hz
Number of Poles	Single Pole 3-Way	Wire Size	#14 - #10 AWG

Requires Neutral Wire	No	Indoor/Outdoor	Indoor
Mounting Type	Wall Box	Wire Connection Type	Screw Terminals
Voltage	120 VAC	Load Type	CFL, Halogen, Incandescent, LED