

Catamount® Terminals



Vinyl Insulated Ring Terminals



CAT. NO.	WIRE RANGE	BOLT SIZE	PKG. QTY.
TV18-6R	22-16	#6	50
TV18-8R		#8	50
TV18-10R		#10	50
TV18-14R		1/4"	50
TV18-516R		5/16"	50
TV14-6R	16-14	#6	50
TV14-8R		#8	50
TV14-10R		#10	50
TV14-14R		1/4"	50
TV14-516R		5/16"	50
TV14-38R		3/8"	50
TV10-6R	12-10	#6	25
TV10-8R		#8	25
TV10-10R		#10	25
TV10-14R		1/4"	25
TV10-516R		5/16"	25
TV10-38R		3/8"	25
TV10-12R		1/2"	25
TV8-8R	8 AWG	#8	10
TV8-10R		#10	10
TV8-14R		1/4"	10
TV8-516R		5/16"	10
TV8-38R		3/8"	10
TV8-12R		1/2"	10
TV6-10R	6 AWG	#10	10
TV6-14R		1/4"	10
TV6-516R		5/16"	10
TV6-38R		3/8"	10
TV6-12R		1/2"	10

\*8 AWG 25 to a package \*\*6 AWG 10 to a package

Vinyl Insulated Fork Terminals



CAT. NO.	WIRE RANGE	BOLT SIZE	PKG. QTY.
TV18-6F	22-16	#6	50
TV18-8F		#8	50
TV18-10F		#10	50
TV18-14F		1/4"	50
TV14-6F	16-14	#6	50
TV14-8F		#8	50
TV14-10F		#10	50
TV14-14F		1/4"	50
TV10-6F	12-10	#6	25
TV10-8F		#8	25
TV10-10F		#10	25
TV10-14F		1/4"	25
TV10-516F		5/16"	25



Non-Insulated Fork Terminals



CAT. NO.	WIRE RANGE	BOLT SIZE	PKG. QTY.
T18-6F	22-16	#6	50
T18-8F		#8	50
T18-10F		#10	50
T14-6F	16-14	#6	50
T14-8F		#8	50
T14-10F		#10	50
T10-6F	12-10	#6	25
T10-8F		#8	25
T10-10F		#10	25
T10-14F		1/4"	25

Non-Insulated Locking Fork Terminals



CAT. NO.	WIRE RANGE	BOLT SIZE	PKG. QTY.
T18-6LF	22-16	#6	50
T18-8LF		#8	50
T18-10LF		#10	50
T14-6LF	16-14	#6	50
T14-8LF		#8	50
T14-10LF		#10	50
T10-6LF	12-10	#6	25
T10-8LF		#8	25
T10-10LF		#10	25



Vinyl Insulated Butt Splices



CAT. NO.	WIRE RANGE	PKG. QTY.
TV18-BS	22-18	50
TV14-BS	16-14	50
TV10-BS	12-10	25



Nylon Wire Joints



CAT. NO.	WIRE RANGE	STD. PKG. QTY.
TN18-WJ	22-16	50
TN14-WJ	16-14	50
TN10-WJ	12-10	25



Non-Insulated Ring Terminals



CAT. NO.	WIRE RANGE	BOLT SIZE	PKG. QTY.
T18-6R	22-16	#4-#6	50
T18-8R		#8	50
T18-10R		#10	50
T14-6R	16-14	#6	50
T14-8R		#8	50
T14-10R		#10	50
T10-6R	12-10	#6	25
T10-8R		#8	25
T10-10R		#10	25
T10-14R		1/4"	25

Vinyl Insulated Locking Fork Terminals



CAT. NO.	WIRE RANGE	BOLT SIZE	PKG. QTY.
TV18-6LF	22-16	#6	50
TV18-8LF		#8	50
TV18-10LF		#10	50
TV14-6LF	16-14	#6	50
TV14-8LF		#8	50
TV14-10LF		#10	50
TV10-6LF	12-10	#6	25
TV10-8LF		#8	25
TV10-10LF		#10	25



Multiple Quick Splices

CAT. NO.	WIRE RANGE	PKG. QTY.
TV18-00QS	22-16	50
TV14-00QS	16-14	50
TV10-00QS	12-10	25

United States  
Tel: 901.252.8000  
800.816.7809  
Fax: 901.252.1354

Canada  
Tel: 450.347.5318  
Fax: 450.347.1976

Technical Services  
Tel: 888.862.3289

Thomas & Betts

www.tnb.com

Catamount® Terminals



Vinyl Insulated Female Disconnects — 250 Series 

CAT. NO.	WIRE RANGE	PKG. QTY.
TV18-250FD	22-16	50
TV14-250FD	16-14	50
TV10-250FD	12-10	25



Nylon Fully Insulated Female Disconnects — 250 Series 

CAT. NO.	WIRE RANGE	PKG. QTY.
TNF18-250FD	22-16	50
TNF14-250FD	16-14	50
TNF10-250FD	12-10	25



Vinyl Fully Insulated Female Disconnects — 250 Series 

CAT. NO.	WIRE RANGE	PKG. QTY.
TVF18-250FD	22-16	50
TVF14-250FD	16-14	50
TVF10-250FD	12-10	25



Vinyl Insulated Male Disconnects — 250 Series 

CAT. NO.	WIRE RANGE	PKG. QTY.
TV18-250MD	22-16	50
TV14-250MD	16-14	50
TV10-250MD	12-10	25



Nylon Fully Insulated Male Disconnects — 250 Series 

CAT. NO.	WIRE RANGE	PKG. QTY.
TNF18-250MD	22-16	50
TNF14-250MD	16-14	50
TNF10-250MD	12-10	25



Vinyl Insulated Piggyback Disconnects — 250 Series 

CAT. NO.	WIRE RANGE	PKG. QTY.
TV18-250PD	22-16	50
TV14-250PD	16-14	50
TV10-250PD	12-10	25



Vinyl Fully Insulated Female Bullet Connectors — 4mm (.156") 

CAT. NO.	WIRE RANGE	PKG. QTY.
TVF18-4FB	22-16	50



Nylon Fully Insulated Female Bullet Connectors 

CAT. NO.	WIRE RANGE	PKG. QTY.
TNF18-4FB	22-16	50
TNF14-4FB	16-14	50



Vinyl Insulated Straight Blade Terminals 

CAT. NO.	WIRE RANGE	PKG. QTY.
TV18-10BL	22-16	50
TV18-18BL		50
TV14-10BL	16-14	50
TV14-18BL		50
TV10-10BL	12-10	25



Vinyl Insulated Male Bullet Connectors — 4mm (.156") 

CAT. NO.	WIRE RANGE	PKG. QTY.
TV18-4MB	22-16	50
TV14-4MB	16-14	50



Fully Insulated Nylon Male Bullet Connectors 

CAT. NO.	WIRE RANGE	PKG. QTY.
TNF18-4MB	22-16	50
TNF14-4MB	16-14	50



Vinyl Insulated Straight Pin Terminals 

CAT. NO.	WIRE RANGE	PKG. QTY.
TV18-12PT	22-16	50
TV14-12PT	16-14	50
TV10-14PT	12-10	25

Catamount® Terminals



Vinyl Insulated Ring Terminals



CAT. NO.	WIRE RANGE	BOLT SIZE	PKG. QTY.
TV18-6R	22-16	#6	50
TV18-8R		#8	50
TV18-10R		#10	50
TV18-14R		1/4"	50
TV18-516R		5/16"	50
TV14-6R	16-14	#6	50
TV14-8R		#8	50
TV14-10R		#10	50
TV14-14R		1/4"	50
TV14-516R		5/16"	50
TV14-38R		3/8"	50
TV10-6R	12-10	#6	25
TV10-8R		#8	25
TV10-10R		#10	25
TV10-14R		1/4"	25
TV10-516R		5/16"	25
TV10-38R		3/8"	25
TV10-12R		1/2"	25
TV8-8R	8 AWG	#8	10
TV8-10R		#10	10
TV8-14R		1/4"	10
TV8-516R		5/16"	10
TV8-38R		3/8"	10
TV8-12R		1/2"	10
TV6-10R	6 AWG	#10	10
TV6-14R		1/4"	10
TV6-516R		5/16"	10
TV6-38R		3/8"	10
TV6-12R		1/2"	10

\*8 AWG 25 to a package \*\*6 AWG 10 to a package

Vinyl Insulated Fork Terminals



CAT. NO.	WIRE RANGE	BOLT SIZE	PKG. QTY.
TV18-6F	22-16	#6	50
TV18-8F		#8	50
TV18-10F		#10	50
TV18-14F		1/4"	50
TV14-6F	16-14	#6	50
TV14-8F		#8	50
TV14-10F		#10	50
TV14-14F		1/4"	50
TV10-6F	12-10	#6	25
TV10-8F		#8	25
TV10-10F		#10	25
TV10-14F		1/4"	25
TV10-516F		5/16"	25



Non-Insulated Fork Terminals



CAT. NO.	WIRE RANGE	BOLT SIZE	PKG. QTY.
T18-6F	22-16	#6	50
T18-8F		#8	50
T18-10F		#10	50
T14-6F	16-14	#6	50
T14-8F		#8	50
T14-10F		#10	50
T10-6F	12-10	#6	25
T10-8F		#8	25
T10-10F		#10	25
T10-14F		1/4"	25

Non-Insulated Locking Fork Terminals



CAT. NO.	WIRE RANGE	BOLT SIZE	PKG. QTY.
T18-6LF	22-16	#6	50
T18-8LF		#8	50
T18-10LF		#10	50
T14-6LF	16-14	#6	50
T14-8LF		#8	50
T14-10LF		#10	50
T10-6LF	12-10	#6	25
T10-8LF		#8	25
T10-10LF		#10	25



Vinyl Insulated Butt Splices



CAT. NO.	WIRE RANGE	PKG. QTY.
TV18-BS	22-18	50
TV14-BS	16-14	50
TV10-BS	12-10	25



Nylon Wire Joints



CAT. NO.	WIRE RANGE	STD. PKG. QTY.
TN18-WJ	22-16	50
TN14-WJ	16-14	50
TN10-WJ	12-10	25



Non-Insulated Ring Terminals



CAT. NO.	WIRE RANGE	BOLT SIZE	PKG. QTY.
T18-6R	22-16	#4-#6	50
T18-8R		#8	50
T18-10R		#10	50
T14-6R	16-14	#6	50
T14-8R		#8	50
T14-10R		#10	50
T10-6R	12-10	#6	25
T10-8R		#8	25
T10-10R		#10	25
T10-14R		1/4"	25

Vinyl Insulated Locking Fork Terminals



CAT. NO.	WIRE RANGE	BOLT SIZE	PKG. QTY.
TV18-6LF	22-16	#6	50
TV18-8LF		#8	50
TV18-10LF		#10	50
TV14-6LF	16-14	#6	50
TV14-8LF		#8	50
TV14-10LF		#10	50
TV10-6LF	12-10	#6	25
TV10-8LF		#8	25
TV10-10LF		#10	25



Multiple Quick Splices

CAT. NO.	WIRE RANGE	PKG. QTY.
TV18-00QS	22-16	50
TV14-00QS	16-14	50
TV10-00QS	12-10	25

United States  
Tel: 901.252.8000  
800.816.7809  
Fax: 901.252.1354

Canada  
Tel: 450.347.5318  
Fax: 450.347.1976

Technical Services  
Tel: 888.862.3289

Thomas & Betts

www.tnb.com



Catamount® Terminals



Vinyl Insulated Female Disconnects — 250 Series 

CAT. NO.	WIRE RANGE	PKG. QTY.
TV18-250FD	22-16	50
TV14-250FD	16-14	50
TV10-250FD	12-10	25



Nylon Fully Insulated Female Disconnects — 250 Series 

CAT. NO.	WIRE RANGE	PKG. QTY.
TNF18-250FD	22-16	50
TNF14-250FD	16-14	50
TNF10-250FD	12-10	25



Vinyl Fully Insulated Female Disconnects — 250 Series 

CAT. NO.	WIRE RANGE	PKG. QTY.
TVF18-250FD	22-16	50
TVF14-250FD	16-14	50
TVF10-250FD	12-10	25



Vinyl Insulated Male Disconnects — 250 Series 

CAT. NO.	WIRE RANGE	PKG. QTY.
TV18-250MD	22-16	50
TV14-250MD	16-14	50
TV10-250MD	12-10	25



Nylon Fully Insulated Male Disconnects — 250 Series 

CAT. NO.	WIRE RANGE	PKG. QTY.
TNF18-250MD	22-16	50
TNF14-250MD	16-14	50
TNF10-250MD	12-10	25



Vinyl Insulated Piggyback Disconnects — 250 Series 

CAT. NO.	WIRE RANGE	PKG. QTY.
TV18-250PD	22-16	50
TV14-250PD	16-14	50
TV10-250PD	12-10	25



Vinyl Fully Insulated Female Bullet Connectors — 4mm (.156") 

CAT. NO.	WIRE RANGE	PKG. QTY.
TVF18-4FB	22-16	50



Nylon Fully Insulated Female Bullet Connectors 

CAT. NO.	WIRE RANGE	PKG. QTY.
TNF18-4FB	22-16	50
TNF14-4FB	16-14	50



Vinyl Insulated Straight Blade Terminals 

CAT. NO.	WIRE RANGE	PKG. QTY.
TV18-10BL	22-16	50
TV18-18BL		50
TV14-10BL	16-14	50
TV14-18BL		50
TV10-10BL	12-10	25



Vinyl Insulated Male Bullet Connectors — 4mm (.156") 

CAT. NO.	WIRE RANGE	PKG. QTY.
TV18-4MB	22-16	50
TV14-4MB	16-14	50



Fully Insulated Nylon Male Bullet Connectors 

CAT. NO.	WIRE RANGE	PKG. QTY.
TNF18-4MB	22-16	50
TNF14-4MB	16-14	50



Vinyl Insulated Straight Pin Terminals 

CAT. NO.	WIRE RANGE	PKG. QTY.
TV18-12PT	22-16	50
TV14-12PT	16-14	50
TV10-14PT	12-10	25