



Powering Business Worldwide

pe.eaton.com

Arrow Hart Tamper & Weather Resistant Self-test GFCI Receptacle

TWRSGF20W

UPC:032664743030

Dimensions:

- **Height:** 4.614 IN
- **Length:** 2.025 IN
- **Width:** 2.877 IN

Weight:.41 LB

Warranties: No Data

Specifications:

- **Amperage Rating:** 20A
- **Voltage Rating:** 125V
- **Wiring Method:** Back wire and side wire
- **Circuit Interrupter Type:** GFCI
- **Color:** White
- **Contact Material:** Brass
- **Device Type:** Receptacle
- **Environmental Conditions:** Tamper and weather resistant
- **Face/Body Material:** PVC
- **Nema Configuration:** 5-20R
- **Receptacle Type:** Two-pole, three-wire, grounding

Supporting documents: No Data

Certifications:

- cULus Listed

Product compliance: No Data

