



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street
75964-7263, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



TY5232MX Locking Cable Tie

Thomas&Betts-Abb Ins Prod

Catalog Number	TY5232MX
Manufacturer	Thomas&Betts-Abb Ins Prod
Description	
Weight per unit	0.0019 (lbs/each)
Product Category	Cable Ties & Wraps

Features

Bundle Diameter	0.08 Inches/2mm-1.97 Inches/50mm
Material	Nylon/Polyamide 6.6
Tensile Strength	18 Pounds/80 Newtons

Material, Color, and Finish

Color	BLACK
-------	-------

Dimensions and Weight

Length	8.0 Inches/203.2mm
Thickness	0.05 Inches/1.10mm
Width	0.10 Inches/2.54mm

Descriptions

Description	LOCKING CABLE TIE
Product Type	Cable Tie 18LB 8IN Uv BLK 2-PC Dist
Special Features	Low profile head is designed to prevent snags on uneven surfaces and easier to pull through bulkheads. Non-magnetic stainless steel locking device insures both maximum strength and the right tightness every time.

Manufacturer Information

Brand	Ty-Rap
GTIN	00786210839370
Manufacturers Part Number	TY5232MX
UPC	786210839370

Taxonomies, Classifications, and Categories

Category Description	WIRE LUBE, MARKERS, & TIES
Type	Standard IN

Availability


minimum qty	100
-------------	-----

Packaging

Carton	100
Package	500
Weight Per each	0.0019

Ty-Rap® High-Performance Nylon Cable Ties

Ty-Rap® 6.6 Nylon Cable Ties — Weather-Resistant Black



STD. PKG. CAT. NO.	BULK PKG. CAT. NO.	BODY WIDTH IN./MM	LENGTH IN./MM	MAX. WIRE BUNDLE DIA. IN./MM	MILITARY STANDARD PART NO.	TENSILE STRENGTH LBS./N	STD. PKG. QTY.	BULK PKG. QTY.
TY523MX	TY23MX	.09/2.29	3.62/91.95	.63/16.00	MS3367-4	18/80.07	100	1,000
TY52315MX	TYB2315MX	.09/2.29	7.00/177.80	1.50/38.10	—	18/80.07	100	1,000
TY5232MX	TY232MX	.09/2.29	8.00/203.20	2.00/50.80	—	18/80.07	100	1,000
TY5234MX	TY234MX	.09/2.29	14.00/355.60	4.00/101.60	—	18/80.07	100	1,000
TY524MX	TY24MX	.14/3.56	5.50/139.70	1.13/28.70	MS3367-5	40/177.90	100	1,000
TY5242MX	TY242MX	.14/3.56	8.19/208.03	2.00/50.80	—	40/177.90	100	1,000
TY526MX	TY26MX	.14/3.56	11.10/281.94	3.00/76.20	—	30/133.40	100	1,000
TY5244MX	TY244MX	.14/3.56	14.50/368.30	4.00/101.60	—	30/133.40	100	1,000
TY525MX	TY25MX	.19/4.83	7.31/185.67	1.75/44.45	MS3367-1	50/222.40	100	1,000
TY5253MX	TY253MX	.19/4.83	11.60/294.64	3.00/76.20	MS3367-7	50/222.40	100	1,000
TY528MX	TY28MX	.19/4.83	14.20/360.68	4.00/101.60	MS3367-2	50/222.40	100	1,000
TY5272MX†	TY272MX†	.27/6.86	8.75/222.250	2.00/50.80	—	120/533.80	50	500
TY527MX†	TY27MX†	.27/6.86	13.40/340.36	3.50/88.90	MS3367-3	120/533.80	50	500
TY5275MX	TY275MX	.27/6.86	18.00/457.20	5.00/127.00	—	120/533.80	50	500
TY5277MX	TY277MX	.27/6.86	24.30/617.22	7.00/177.80	—	120/533.80	50	500
TY529MX*	TY29MX*	.27/6.86	30.00/762.00	9.00/228.60	MS3367-6	120/533.80	50	500
TY53510MX†	—	.32/8.13	35.00/889.00	10.00/254.00	—	175/778.40	50	—
TY54513MX†	—	.32/8.13	45.00/1,143.00	13.00/330.20	—	175/778.40	50	—

For use in temperatures ranging from -40° F to 185° F (-40° C to 85° C).

* For military compliance of weather-resistant black 120-lb. ties, replace suffix X with O (i.e., TY27M-O).

† Not Listed or Recognized Models.

- UL® File No. E49405
- Installation tools available on pp. C-46–C-48.

Increase efficiency! Ty-Rap Tote® Cable Tie Dispensers



Attach to your belt or almost any other convenient location via a built-in belt clip and chrome steel loop.

Includes 100 genuine Ty-Rap® cable ties.

Quickly refill your Ty-Rap Tote® through the hook-and-loop-secured flap.

Easily remove the tie you need through the reinforced, diamond-shaped cut-out while the Ty-Rap Tote® securely holds the rest.

Keep cable ties clean and organized inside the durable, lightweight polyester exterior and tough vinyl interior.



STD. PKG. CAT. NO.	DESCRIPTION	STD. PKG. QTY.
TY-TOTE-25	Ty-Rap Tote® 8" Cable Tie Dispenser (includes 1 pkg. TY525M)	1
TY-TOTE-23	Ty-Rap Tote® 4" Cable Tie Dispenser (includes 1 pkg. TY523M)	1
TY-TOTE-28	Ty-Rap Tote® 11"–14" Cable Tie Dispenser (includes 1 pkg. TY528M)	1

Order only genuine Ty-Rap® Cable Ties to refill your dispenser!