



Representative Image

Catalog No. U013

Description: 30A SURFACE UNMTRD

UPC No 784567567502

Home > Power Outlets > Power Outlets

Midwest Electric's Temporary Power and Power Outlets are a means of providing power required by various construction trades, residential sites, and mobile electrical applications. Temporary Power and Power Outlets offer one or more receptacles, with or without overcurrent protection, disconnecting, metering, and/or pedestal mounting functions, in a single enclosure of G-90 zinc-coated steel. The NEMA 3R rainproof enclosure is lockable and engineered to provide maximum protection against weather, vandalism, and normal field use.

Descriptors

Category	Power Outlets
----------	---------------

Specifications

Mounting	Surface
Heads	1
Metering	Unmetered
Receptacles	TTR-30(R32U)
Feed	Overhead
AIC	10,000
Amps	30
Cabinet Size	5 in. W X 7 in. H
Circuit Protection	No
Hub Provision	Yes
Installed Breaker	None
Load Center	None
Loop Feed	No
Phase	1
Suitable for Service Equipment	No
Unit Weight	4.5 lb
Volts	120

Classifications

Standard Package	4
Stock Class Code	Stock

Approvals

Certification	UL/CUL
---------------	--------

Publications

Title	Publication No.	Publication Type
Storm Season Brochure This brochure highlights the most popular products sold during storm season.	MET1005	Brochures
Storm Season Brochure This brochure highlights the most popular products sold during storm season.	005	Brochures
U013 OUTLINE DRAWING MIDWEST POWER OUTLET UNMETERED SURFACE UL LISTED 30A 120V 1PH G90 N3R OUTLINE DRAWING	U013	Drawings-Outline and Dimensional
Durable Outdoor Power Outlets power the great outdoors!	MET-007A	Brochures
Heavy Duty Power Outlets 2 pages. MET-020 Rev. B.	MET-020A	Brochures

Additional Documentation: Visit our Publication Library to find technical documentation, time current curves, CSI Specifications and promotional literature.