

Catalog Number: U1980-O

UPC Code:

Item Description: 200A 4T RL SWY UG

784572134508

Brand Name: Milbank

Type: Ringless Meter Socket

Application: Meter Socket

Standard: UL Listed

Voltage Rating: 600 Volts Alternating Current

Amperage Rating: 200 Continuous Ampere

Phase: 1 Phase

Frequency Rating: 60 Hertz

Number Of Cutouts: 0

Cable Entry: Underground, Side Wireway

Terminal: Single Lay in Line Side and Load Side

Connectors

Mounting: Surface Mount

Enclosure: Type 3R, G90 Galvanized Steel with


Powder Coat Finish


Additional Specifications: Number of Jaws:4 Terminal


Hub Opening and Closing Plates:Plain Top




Г	FEATURE TABLE		
I	TEM	QTY	DESCRIPTION
	Α	5	U/L MNTG.EMBOSS
	В	1	1/4, 1/2 CONC. K.O.
	С	1	34, 1, 114, 11/2 CONC. K.O.
	D	4	11/4, 11/2, 2, 21/2 CONC. K.O.
	Е	1	2½, 3, 3½ CONC. K.O.
_		•	2/2, 0, 0/2 00.10.11.0.











Version:

All dimensions are +/- 1/16". Drawing views are not to scale.

1

Utility requirements for this equipment may vary. Always consult the serving utility for their requirements prior to ordering or installing this equipment. This product must be installed by a licensed electrician. Installation of this equipment may require local electrical inspector approval.