



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



U2594X 320A 3PH Oh/Ug 7T HD LVR Bypass Meter Socket

Milbank

Catalog Number	U2594X
Manufacturer	Milbank
Description	Meter Socket, 320 A, 34-1/8 In Overall Height, 19 In Overall Width, 6-1/2 In Overall Length, Surface Mount, 3 Phases, Large Closing Plate Hub, 7 Jaws, 4 Wires, 600 V Ac, Overhead/Underground Feed, 56 LB
Weight per unit	56.0 (lbs/each)
Product Category	Residential Single Meter Socke

Features

amperage rating	320 Continuous Ampere
Bypass Type	Lever Bypass
Cable Entry	Overhead and Underground and Side Wireway
cutout size	No Main Breaker
insulation	Glass Polyester
Phase	3 Phase

Dimensions and Weight

Size	6.5L x 19W x 34.125H
------	----------------------

Descriptions

Also Known As...	Meter Box
	Meter Socket
Description	320A 3PH OH/UG 7T HD LVR BYPASS METER SOCKET
extra long description	MILB U2594-X 320A 7T RL SWY STUD HD

Manufacturer Information

Brand	MILBANK
GTIN	00784572135529
UPC	784572135529

Taxonomies, Classifications, and Categories

Category Description	Meter Sockets
Type	Ringless Meter Socket

Packaging

Carton	1
Weight Per each	56



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Enclosure	G90 Galvanized Steel with Powder Coat Finish
Frequency Rating	60 Hertz
Mounting	Surface Mount
standard	UL Listed;Type 3R