

Catalog Number: Item Description: UPC Code:

U5059-X-2/200-K3L 320A 4T RL OU HD LVR MAIN 784572368910

| Brand Name: | Milbank | |
|----------------------------|--|-------------------------------|
| Туре: | Ringless M | leter Socket |
| Application: | Meter Soc | ket With Main |
| Standard: | UL Listed | |
| Voltage Rating: | Up to 240 ' | Volts Alternating Current |
| Amperage Rating: | 320 Contir | nuous Ampere |
| Phase: | 1 Phase | |
| Frequency Rating: | 60 Hertz | |
| Number Of Cutouts: | 2 | |
| Cutout Size: | 200 Ampere Main Breaker, 200 Ampere Main Breaker | |
| Cable Entry: | Overhead and Underground | |
| Terminal: | Single Mechanical Line Side and Single Mechanical Load Side | |
| Mounting: | Surface Mount | |
| Enclosure: | Type 3R, G90 Galvanized Steel with Powder Coat Finish | |
| Additional Specifications: | | Number of Jaws:4 Terminal |
| | | Hub Opening and Closing Plate |
| | | Hub Opening and Closing Plate |
| | | |



tes:Large Closing Plate

tes:Large Closing Plate

Hub Opening and Closing Plates:Large Closing Plate

Hub Opening and Closing Plates:Large Closing Plate

Hub Opening and Closing Plates:Large Closing Plate

Utility requirements may vary. Always consult the serving utility for their requirements prior to ordering or installing this equipment. This product must always be installed by a licensed electrician. Installation of this equipment may require local electrical inspector approval.

| FEATURE TABLE | | |
|---------------|-----|--------------------------------|
| ITEM | QTY | DESCRIPTION |
| А | 8 | STD. MNTG. EMBOSS |
| В | 1 | 1/4 SOLID K.O. |
| С | 1 | 1/4, 1/2 CONC. K.O. |
| D | 6 | 1, 1¼, 1½, 2, 2½, 3 CONC. K.O. |

