



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



U9701XQGHSP 7 Term RNLGS LRG CLS PLT Quadplex GND LVR Byps STN *Milbank*

Catalog Number	U9701XQGHSP
Manufacturer	Milbank
Description	7 Term RNLGS LRG CLS PLT Quadplex GND LVR Byps STN-STL HSP
Weight per unit	22.0 (lbs/each)
Product Category	Commercial Single Meter Socket

Features

amperage rating	200 Continuous Ampere
Bypass Type	Lever Bypass
Cable Entry	Overhead or Underground
cutout size	No Main Breaker
insulation	Glass Polyester
Phase	3 Phase
Voltage Rating	600 Volts Alternating Current

Dimensions and Weight

Size	4.844L x 13W x 19H
------	--------------------

Descriptions

Description	7 TERM RNLGS LRG CLS PLT QUADPLEX GND LVR BYPS STN
extra long description	MILB U9701-X-QG-HSP 200A 7T RL HD L
Long Description	7 TERM RNLGS LRG CLS PLT QUADPLEX GND LVR BYPS STN-STL HSP
Product Type	200A 7T RL HD LVR Ou 29277

Manufacturer Information

Brand	MILBANK
Manufacturers Part Number	U9701-X-QG-HSP

Taxonomies, Classifications, and Categories

Type	Ringless Meter Socket
------	-----------------------

Packaging

Carton	1
Weight Per each	22

Uses, Certifications, and Standards

Application	Meter Socket
Enclosure	G90 Galvanized Steel with Powder Coat Finish
Frequency Rating	60 Hertz
Mounting	Surface Mount
standard	UL Listed;Type 3R