



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

110 Success Blvd
79029-0000, TX Dumas
Phone: 806-934-4805
Fax: 806-717-2052



UAG1 1" Ua Sealtite Conduit, Bonded UL 100' *Southwire Company*

Catalog Number	UAG1
Manufacturer	Southwire Company
Description	Liquidtight Flexible Conduit, 1 In Trade Size, 1.29 to 1.315 In Conduit Outer Diameter, 1.041 to 1.066 In Conduit Inner Diameter, TITAN2(TM) UL Style, 100 FT Length, Jacket: Thermoplastic;Core: Steel, Hot Dip Galvanized, Gray, 6.5 In Bend Radius, -67 °F Operating Temperature, +176 °F Operating Temperature, 60 LB/100 FT
Weight per unit	0.6000 (lbs/each)
Product Category	Liquid Tight Conduit

Features

outside diameter	1305
------------------	------

Descriptions

Description	1" UA SEALTITE CONDUIT, BONDED UL
extra long description	SWC 55093003 Titan2 Type UL Liquidt

Manufacturer Information

GTIN	00032886042430
UPC	032886042430

Taxonomies, Classifications, and Categories

Category Description	Liquid Tight
Type	LTM-UL

Packaging

Carton	100
Weight Per each	0.6