



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

760 Ford St.
80915-0000, CO Colorado Springs
Phone: 719-559-2456
Fax: 719-867-4287



UAG1 1" Ua Sealtite Conduit, Bonded UI 100' *Southwire Company*

Catalog Number	UAG1
Manufacturer	Southwire Company
Description	Liquidtight Flexible Conduit, 1 In Trade Size, 1.29 to 1.315 In Conduit Outer Diameter, 1.041 to 1.066 In Conduit Inner Diameter, TITAN2(TM) UI Style, 100 FT Length, Jacket: Thermoplastic;Core: Steel, Hot Dip Galvanized, Gray, 6.5 In Bend Radius, -67 °F Operating Temperature, +176 °F Operating Temperature, 60 LB/100 FT
Weight per unit	0.6000 (lbs/each)
Product Category	Liquid Tight Conduit

Descriptions

Description	1" UA SEALTITE CONDUIT, BONDED UL
extra long description	SWC 55093003 LTM-UL 1" GYJT 100C

Manufacturer Information

GTIN	00032886042430
UPC	032886042430

Taxonomies, Classifications, and Categories

Category Description	Liquid Tight
----------------------	--------------

Packaging

Carton	100
Weight Per each	0.6