



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

UAG112 1-1/2" Ua Sealtite Conduit, Bonded UI 50'

Southwire Company

Catalog Number	UAG112
Manufacturer	Southwire Company
Description	Liquidtight Flexible Conduit, 1-1/2 In Trade Size, 1.865 to 1.90 In Conduit Outer Diameter, 1.575 to 1.6 In Conduit Inner Diameter, TITAN2(TM) UI Style, 50 FT Length, Jacket: Thermoplastic;Core: Steel, Hot Dip Galvanized, Gray, 9 In Bend Radius, -67 °F Operating Temperature, +176 °F Operating Temperature, 113 LB/100 FT
Weight per unit	1.1 (lbs/each)
Product Category	Liquid Tight Conduit

Descriptions

Description	1-1/2" UA SEALTITE CONDUIT, BONDED UL 50'
extra long description	SWC 55093205 LTM-UL 1-1/2" GYJT 50C

Manufacturer Information

GTIN	00032886042355
UPC	032886042355

Taxonomies, Classifications, and Categories

Category Description	Liquid Tight
----------------------	--------------

Packaging

Carton	50
Weight Per each	1.13