

# Eaton UASTS131C226CH

Catalog Number: UASTS131C226CH

Eaton meter socket, Instrument rated socket, 20A, Over/under, 3-5/16 inch hub cover plate, 13-jaw, 3-ph, Factory wired test switch, Gnd conn (#14-#2 Cu), Al, Triplex, 4-wire, Ringless, 600 Vac



Photo is representative

## General specifications

### Product Name

Eaton meter socket

### Catalog Number

UASTS131C226CH

### UPC

786685216409

### Product Length/Depth

4.35 in

### Product Height

20 in

### Product Width

12 in

### Product Weight

18 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Certifications

UL Listed

## defaultTaxonomyAttributeLabel

### Type

Instrument rated socket

### Amperage Rating

20A

### Feed type

Top/bottom

### Number of jaws

13-jaw

### Phase

Three-phase

### Enclosure material

Aluminum

### Number of wires

Four-wire

### Hub type

3-5/16 in hub cover plate

### Security

Ringless

### Voltage rating

600 V

### Accessories

Factory wired test switch

### Number of sockets

1

## Resources

### Brochures

[Single Meter Sockets](#)

### Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

### Drawings

[Dimensional Drawing - SKT/SW 20A 13T FW HCP](#)

### Specifications and datasheets

[Eaton Specification Sheet - UASTS131C226CH](#)