



UC 50 \updownarrow CF30 - CF54 \leftrightarrow 50 mm

		<p>BTRCC 6X20 x1</p> <p>110</p>										
<p>UC 50</p> <p>(mm)</p>	<p>UC 50</p>	<table border="1"> <thead> <tr> <th>\downarrow daN</th> <th>GS</th> <th>GC</th> <th>304L</th> <th>316L</th> </tr> </thead> <tbody> <tr> <td>12</td> <td>586 040</td> <td>586 043</td> <td>586 048</td> <td>586 044</td> </tr> </tbody> </table>	\downarrow daN	GS	GC	304L	316L	12	586 040	586 043	586 048	586 044
\downarrow daN	GS	GC	304L	316L								
12	586 040	586 043	586 048	586 044								



UC 50 \updownarrow CF30 - CF54 \leftrightarrow 50 mm

		<p>CF30</p> <p>CF54</p> <p>BTRCC 6X20 x1</p> <p>110</p>										
<p>UC 50</p> <p>(mm)</p> <p>15x7 30x7 Ø5 45 70,4 35</p>	<p>UC 50</p>	<table border="1"> <thead> <tr> <th>\downarrow daN</th> <th>GS</th> <th>GC</th> <th>304L</th> <th>316L</th> </tr> </thead> <tbody> <tr> <td>12</td> <td>586 040</td> <td>586 043</td> <td>586 048</td> <td>586 044</td> </tr> </tbody> </table>	\downarrow daN	GS	GC	304L	316L	12	586 040	586 043	586 048	586 044
\downarrow daN	GS	GC	304L	316L								
12	586 040	586 043	586 048	586 044								