Intended Use • Up to 80% of energy savings vs. fluorescent and xenon RAYZER Provides task or accent lighting in commercial, retail, hospitality • Multiple installation options and residential applications. Ideal for use under and over cabinets, display cases, task lighting, office lighting, coves and utility/work Modular LED Lighting System • Linkable functionality areas. • Slim profile - only 1/2" in height Features • Requires 24V step down transformer kit (sold separately) • Replaces up to a 17W T8 • Available in 9", 12", 18" and 24" lengths • Durable aluminum construction in a low-profile design. Can be plugged in or direct-wired (splice box and 24" connector cord Listings required for direct-wiring) cUL Listed to U.S. and Canadian safety standards.



ORDERING INFORMATION Specifications subject to change.	DRMATION Specifications subject to change.	
Series	Options	
RAZ99" length - 3 LEDsRAZ1212" length - 4 LEDsRAZ1818" length - 6 LEDsRAZ2424" length - 8 LEDs	Consult factory.	

ADDITIONAL INFORMATION

For additional product information, visit www.lithonia.com.

	ACCESSORIES/REPLACEMENT PARTS	
RAZTRANS24 120	24V transformer - 120V power source	
RAZTRANS24 MVOLT	24V transformer- Multi-Volt power source	
RAZDIM	Step dimmer with remote touch pad	
RAZ CC121	121" Linking cord (fixture to fixture)	
RAZ CC24	24" linking cord (fixture to fixture)	
RAZ CC3	3" linking cord (fixture to fixture)	
RAZLVCC	Low voltage linking cord (cord to cord)	
RAZ ERC	End row connector	
RAZ PHD	Power hub distributor	
RAZ INLS26	In-line power switch	
UCD JB	Splice box - white (required for direct wire)	
UCD JB BL	Splice box - black (required for direct wire)	
UC ERC24 R12	24" connector cord - white (required for direct wire)	
UC ERC24 BL	24" connector cord - black (required for direct wire)	

Specifications Length: RAZ9 - 9-1/4 (23.5) RAZ12 - 12-1/4 (31.1) RAZ18 - 18-1/4 (46.4) RAZ24 - 24-1/4 (61.6) Width: 1-1/4 (3.18) Height: 1/2" (1.27)

All dimensions are inches (centimeters)

522

Notes

Lamps not included.
Use with non-dimmable switches only.

🔰 🚺 LITHONIA LIGHTING